

## Die, HSSE M right, pre-slotted and 2.0 thread chamfer

For universal use up to 1300 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

For tapping metric male threads in the steel, stainless steel, NF metal and special alloy material groups up to a strength of 1300 N/mm<sup>2</sup>.

### Version:

- Right-handed thread-cutting die, tol. 6g, pre-slotted and 2.0 threaded chamfer

### Advantage:

- Standard geometry with a very good price-performance ratio



Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.		
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC	
	●					●					●	●								

<b>Art. no.</b>	<b>13421 160</b>
<b>Thread type</b>	Metric thread
<b>Cutting material</b>	HSSE
<b>Tolerance of dies</b>	6 g
<b>Thread type x nominal diameter</b>	M16
<b>Pitch</b>	2 mm
<b>Outer diameter</b>	45 mm
<b>Height</b>	18 mm
<b>Cutting direction</b>	Right-hand cutting

### EAN-Code

4039247072675