

Shrink-fit chucks 3°

In accordance with ISO 12164 (DIN 69893); slim version

diebold

Application:

For clamping tools with a straight shank.

Execution:

- Slim version for tool mould making.
- Concentricity tolerance of hollow shank taper for location hole $d1 < 0.003$ mm.
- Oxidation-free coating to prevent corrosion during dry machining and to prevent discoloration during shrinking.
- Clamping diameter for h6 shank tolerance.
- Required for internal cooling supply coolant transfer pipe no. 23715.

Delivery:

1x shrink-fit chuck 3° in accordance with ISO 12164 (DIN 69893); slim version.



Art. no.	23421 062
Brand	DIEBOLD
Manufacturer Part Number	72.575.501.300
Tool holding device	HSK 63
Clamping diameter	10 mm
Projecting length	90 mm
Outer diameter	22 mm
Tapered diameter	16 mm
Length	60 mm
Clamp in depth	42 mm
Max. adjustment travel	5 mm
Concentricity tolerance	0.003 mm
Coolant supply	Internal axial
Balancing quality	G 2.5 at 25 rpm
Gross Weight	0.787 kg
Product Group	297