

Safety cabinet CLASSIC line type 90

Fire resistant for 90 minutes



Application:

For safe and legally compliant storage of hazardous materials and flammable liquids in work areas in line with TRGS 510, DIN EN 14470-1 and DIN EN 14727.

Execution:

- External corpus, powder-coated sheet steel, light grey RAL 7035
- Internal corpus made of high quality decorative panels, light grey RAL 7035
- Lockable hinged doors, door front in zinc yellow RAL 1018
- Standard features: height-adjustable tray bases, base tray, 1 perforated insert made from powder coated sheet steel, height-adjustable base
- Hinged doors with standard integrated locking system and temperature monitoring, automatic self-closing in case of fire
- Ventilation and air extraction on each cabinet level
- Viewing window provided for visual check of ventilation shut-off flaps
- Tray bases and base trays are galvanically connected with the cabinet housing – avoids risk of ignition (BGR 132 TRBS 2153)
- Feet adjustable from inside and outside
- Underpinning guaranteed due to removable base

Advantage:

- Tested safety on high level: Prototype testing by MPA, TÜV, GS/CE-marks, fire resistant for 90 minutes and High Quality seal for superior design, user-friendliness and increased service life.
- Fire resistant for 90 minutes



Art. no.	50069 006
Brand	DÜPERTHAL
Manufacturer Part Number	29-200965-030
Model	CLASSIC ONE L
Fire resistance rating	F90
Number of doors	2 PCS
Door design	Full-sheet panel
With single-handed swing door technology	Yes
External height	2080 mm
External width	895 mm
Depth	595 mm
Interior height	1830 mm
Internal width	799 mm
Internal depth	446 mm
With base basin	Yes
Number of tray bases	3 PCS
Colour of front	Zinc yellow RAL 1018
Cabinet colour	Light grey RAL 7035
Gross Weight	358.000 kg
Product Group	5AJ

EAN

4036361087431