

# PRODUCT DATASHEET NAV 50 LED FIL V 3600LM 21W 727 E27

NAV LED FIL V | LED replacement for NAV lamps in design-oriented outdoor applications



#### Areas of application

- Streets
- Area lighting
- Pedestrian zones
- Parks
- Outdoor applications only in suitable luminaires

#### **Product benefits**

- Same design as traditional NAV lamps with frosted, ellipsoid full glass bulb
- Full use of reflector of existing luminaire thanks to 360 degree beam angle
- Saves up to 78 % energy when used as replacement for sodium vapor lamps (NAV)
- Instant 100 % light, no warm-up time
- Similar light distribution as traditional NAV lamps

## **Product features**

- Suitable for operation with conventional control gear (CCG) or 230 V AC mains
- Very high efficiency of up to 190 lm/W
- Power factor: 0.9
- Type of protection: IP65
- Surge protection: up to 2 kV (L-N)



### **TECHNICAL DATA**

#### **Electrical data**

Nominal wattage	21 W
Construction wattage	21.00 W
Nominal voltage	220240 V
Claimed equiv. conventional lamp power	50 W
Nominal current	90 mA
Type of current	AC
Inrush current	6.3 A
Operating frequency	50/60 Hz
Mains frequency	50/60 Hz
Max. lamp no. on circuit break. 10 A (B)	11
Max. lamp no. on circuit break. B10 A - CCG without compensation	10
Max. lamp no. on circuit break. B10 A - CCG with compensation	22
Max. lamp no. on circuit break. 16 A (B)	17
Max. lamp no. on circuit break. B16 A - CCG without compensation	16
Max. lamp no. on circuit break. B16 A - CCG with compensation	35
Total harmonic distortion	15 %
Power factor $\lambda$	> 0.90

#### Photometrical data

Luminous intensity	N/A
Luminous flux	3600 lm
Nominal useful luminous flux 90°	3600 lm
Luminous efficacy	171 lm/W
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Warm White
Color temperature	2700 К
Color rendering index Ra	70
Light color	727
Standard deviation of color matching	≤6 sdcm
Rated LLMF at 6,000 h	0.80
Flickering metric (Pst LM)	1
Stroboscope effect metric (SVM)	0,4



# Light technical data

Beam angle	360 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s
Rated beam angle (half peak value)	360.00 °

#### **Dimensions & Weight**

Overall length	170.00 mm
Diameter	38.00 mm
Maximum diameter	38 mm
Product weight	80.00 g

### Temperatures & operating conditions

Ambient temperature range	-20+50 °C
Maximum temperature at tc test point	80 °C

## Lifespan

Lifespan	25000 h
Number of switching cycles	100000
Lumen maintenance at end of serv	0.70
Rated lamp survival factor at 6,000	≥ 0.90

### Additional product data

Base (standard designation)	E27
Mercury content	0.0 mg

Mercury-free	Yes
Product remark	Available from June 2023

# Capabilities

Dimmable	No

# Certificates & Standards

Energy efficiency class	C <sup>1)</sup>
Energy consumption	21.00 kWh/1000h
Type of protection	IP65
Standards	CE / EAC / UKCA
Photobiological safety group acc. to EN62778	RG1

1) Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

## Country-specific categorizations

Order reference	NAV 50 LED FIL

## LOGISTICAL DATA

## Energy labelling regulation data acc EU 2019/2015

Lighting technology usedLEDNon-directional or directionalNDLSMains or non-mainsMLSLight source cap-type (or other electric interface)E27Connected light source (CLS)NoColor-tuneable light sourceNoEnvelopeNoHigh luminance light sourceNoAnti-glare shieldNoCorrelated colour temperature typeSINGLE_VALUEStandby powerN/ANetworked standby power for CLSN/ALength170.00 mmHeight38.00 mm		
Mains or non-mainsMLSLight source cap-type (or other electric interface)E27Connected light source (CLS)NoColor-tuneable light sourceNoEnvelopeNoHigh luminance light sourceNoAnti-glare shieldNoCorrelated colour temperature typeSINGLE_VALUEStandby powerN/ANetworked standby power for CLSN/AClaim of equivalent powerNoLength170.00 mm	Lighting technology used	LED
Light source cap-type (or other electric interface)   E27     Connected light source (CLS)   No     Color-tuneable light source   No     Envelope   No     High luminance light source   No     Anti-glare shield   No     Correlated colour temperature type   SINGLE_VALUE     Standby power   N/A     Networked standby power for CLS   N/A     Length   170.00 mm	Non-directional or directional	NDLS
Connected light source (CLS)NoColor-tuneable light sourceNoEnvelopeNoHigh luminance light sourceNoAnti-glare shieldNoCorrelated colour temperature typeSINGLE_VALUEStandby powerN/ANetworked standby power for CLSN/AClaim of equivalent powerNoLength170.00 mm	Mains or non-mains	MLS
Color-tuneable light sourceNoEnvelopeNoHigh luminance light sourceNoAnti-glare shieldNoCorrelated colour temperature typeSINGLE_VALUEStandby powerN/ANetworked standby power for CLSN/AClaim of equivalent powerNoLength170.00 mm	Light source cap-type (or other electric interface)	E27
EnvelopeNoHigh luminance light sourceNoAnti-glare shieldNoCorrelated colour temperature typeSINGLE_VALUEStandby powerN/ANetworked standby power for CLSN/AClaim of equivalent powerNoLength170.00 mm	Connected light source (CLS)	No
High luminance light source   No     Anti-glare shield   No     Correlated colour temperature type   SINGLE_VALUE     Standby power   N/A     Networked standby power for CLS   N/A     Claim of equivalent power   No     Length   170.00 mm	Color-tuneable light source	No
Anti-glare shield   No     Correlated colour temperature type   SINGLE_VALUE     Standby power   N/A     Networked standby power for CLS   N/A     Claim of equivalent power   No     Length   170.00 mm	Envelope	No
Correlated colour temperature type   SINGLE_VALUE     Standby power   N/A     Networked standby power for CLS   N/A     Claim of equivalent power   No     Length   170.00 mm	High luminance light source	No
Standby power N/A   Networked standby power for CLS N/A   Claim of equivalent power No   Length 170.00 mm	Anti-glare shield	No
Networked standby power for CLS N/A   Claim of equivalent power No   Length 170.00 mm	Correlated colour temperature type	SINGLE_VALUE
Claim of equivalent power No   Length 170.00 mm	Standby power	N/A
Length 170.00 mm	Networked standby power for CLS	N/A
	Claim of equivalent power	No
Height 38.00 mm	Length	170.00 mm
	Height	38.00 mm
Width     38.00 mm	Width	38.00 mm

Chromaticity coordinate x	0,463
Chromaticity coordinate y	0,42
R9 Colour rendering index	>0
Beam angle correspondence	SPHERE_360
Survival factor	0,9
Displacement factor	0.9
LED light source replaces a fluorescent light source	No
EPREL ID	1371175
Model number	AC46360

## Safety advice

- Not suitable for operation with ignitors
- Operation on the capacitor can lead to a reduction of the power factor of the system.
- When installed horizontally, the t  $_{\rm c}$  point of the lamp is located on the top side of the lamp.
- Use in tight luminaires and luminaires with tight reflectors not recommended.
- Only suitable for temperatures of up to 50°C inside of the luminaire. Use in tight luminaires and luminaires with tight reflectors not recommended.

## DOWNLOAD DATA

	Documents and certificates
PDF	User instruction
PDF	Declarations Of Conformity CE
PDF	Declarations Of Conformity UKCA
	Photometric and lighting design files
1	IES file (IES)
1	LDT file (Eulumdat)
1	UGR file (UGR table)
	LDC typ polar
1	Spectral power distribution

# LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4099854071973	Folding box 1	44 mm x 44 mm x 256 mm	123.00 g	0.50 dm <sup>3</sup>
4099854071980	Shipping box 6	274 mm x 152 mm x 117 mm	900.00 g	4.87 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.