



**SEMITRANS® 2**

## Trench IGBT Modules

**SKM 195GB126D**

**SKM 195GAL126D**


Preliminary Data

### Features

- Trench = Trenchgate technology
- $V_{CE(sat)}$  with positive temperature coefficient
- High short circuit capability, self limiting to  $6 \times I_C$

### Typical Applications

- AC inverter drives
- UPS
- Electronic welders




GB

GAL

Absolute Maximum Ratings		$T_{case} = 25^\circ\text{C}$ , unless otherwise specified		
Symbol	Conditions	Values		Units
<b>IGBT</b>				
$V_{CES}$	$T_j = 25^\circ\text{C}$	1200		V
$I_C$	$T_j = 150^\circ\text{C}$	$T_c = 25^\circ\text{C}$	220	A
		$T_c = 80^\circ\text{C}$	160	A
$I_{CRM}$	$I_{CRM} = 2 \times I_{Cnom}$	300		A
$V_{GES}$		$\pm 20$		V
$t_{psc}$	$V_{CC} = 600\text{ V}; V_{GE} \leq 20\text{ V}; T_j = 125^\circ\text{C}$ $V_{CES} < 1200\text{ V}$	10		$\mu\text{s}$
<b>Inverse Diode</b>				
$I_F$	$T_j = 150^\circ\text{C}$	$T_c = 25^\circ\text{C}$	170	A
		$T_c = 80^\circ\text{C}$	115	A
$I_{FRM}$	$I_{FRM} = 2 \times I_{Fnom}$	200		A
$I_{FSM}$	$t_p = 10\text{ ms}; \text{sin.}$	$T_j = 150^\circ\text{C}$	900	
<b>Freewheeling Diode</b>				
$I_F$	$T_j = 150^\circ\text{C}$	$T_{case} = 25^\circ\text{C}$	170	A
		$T_{case} = 80^\circ\text{C}$	115	A
$I_{FRM}$	$I_{FRM} = 2 \times I_{Fnom}; t_p = 1\text{ ms}$	200		A
$I_{FSM}$	$t_p = 10\text{ ms}; \text{sin.}$	$T_j = 150^\circ\text{C}$	900	
<b>Module</b>				
$I_{t(RMS)}$		200		A
$T_{vj}$		-40 ... +150		$^\circ\text{C}$
$T_{stg}$		-40 ... +125		$^\circ\text{C}$
$V_{isol}$	AC, 1 min.	4000		V

Characteristics		$T_{case} = 25^\circ\text{C}$ , unless otherwise specified			
Symbol	Conditions	min.	typ.	max.	Units
<b>IGBT</b>					
$V_{GE(th)}$	$V_{GE} = V_{CE}; I_C = 6\text{ mA}$	5	5,8	6,5	V
$I_{CES}$	$V_{GE} = 0\text{ V}; V_{CE} = V_{CES}$		0,1	0,3	mA
$V_{CE0}$		$T_j = 25^\circ\text{C}$	1	1,2	V
		$T_j = 125^\circ\text{C}$	0,9	1,1	V
$r_{CE}$	$V_{GE} = 0\text{ V}$	$T_j = 25^\circ\text{C}$	4,7	6,3	m $\Omega$
		$T_j = 125^\circ\text{C}$	7,3	9	m $\Omega$
$V_{CE(sat)}$	$I_{Cnom} = 150\text{ A}; V_{GE} = 15\text{ V}$		1,7	2,15	V
			2	2,45	V
$C_{ies}$	$V_{CE} = 25; V_{GE} = 0\text{ V}$	$f = 1\text{ MHz}$	10,5		nF
$C_{oes}$			0,9		nF
$C_{res}$			0,8		nF
$Q_G$	$V_{GE} = -8\text{ V} \dots +20\text{ V}$	1380		nC	
$R_{Gint}$	$T_j = ^\circ\text{C}$	5		$\Omega$	
$t_{d(on)}$	$R_{Gon} = 2\ \Omega$	$V_{CC} = 600\text{ V}$ $I_{Cnom} = 150\text{ A}$	280		ns
$t_r$			50		ns
$E_{on}$	$R_{Goff} = 2\ \Omega$	$T_j = 125^\circ\text{C}$ $V_{GE} = \pm 15\text{ V}$	16		mJ
$t_{d(off)}$			560		ns
$t_f$			70		ns
$E_{off}$			24,5		mJ
$R_{th(j-c)}$	per IGBT			0,16	K/W



**SEMITRANS® 2**

## Trench IGBT Modules

**SKM 195GB126D**

**SKM 195GAL126D**

Preliminary Data

### Features

- Trench = Trenchgate technology
- $V_{CE(sat)}$  with positive temperature coefficient
- High short circuit capability, self limiting to  $6 \times I_C$


### Typical Applications

- AC inverter drives
- UPS
- Electronic welders

Characteristics		min.	typ.	max.	Units
<b>Inverse Diode</b>					
$V_F = V_{EC}$	$I_{Fnom} = 100 \text{ A}; V_{GE} = 0 \text{ V}$		2	2,5	V
	$T_j = 25 \text{ }^\circ\text{C}_{chiplev.}$				V
	$T_j = 125 \text{ }^\circ\text{C}_{chiplev.}$		1,8		V
$V_{F0}$			1,1	1,2	V
	$T_j = 25 \text{ }^\circ\text{C}$				V
	$T_j = 125 \text{ }^\circ\text{C}$				V
$r_F$			9	13	mΩ
	$T_j = 25 \text{ }^\circ\text{C}$				mΩ
	$T_j = 125 \text{ }^\circ\text{C}$				mΩ
$I_{RRM}$	$I_{Fnom} = 150 \text{ A}$		86		A
$Q_{rr}$	$di/dt = 2200 \text{ A}/\mu\text{s}$		17		μC
$E_{off}$	$V_{GE} = -15 \text{ V}; V_{CC} = 600 \text{ V}$		5,8		mJ
$R_{th(j-c)D}$	per diode			0,32	K/W
<b>Freewheeling diode</b>					
$V_F = V_{EC}$	$I_{Fnom} = 100 \text{ A}; V_{GE} = 0 \text{ V}$		2	2,5	V
	$T_j = 25 \text{ }^\circ\text{C}_{chiplev.}$				V
	$T_j = 125 \text{ }^\circ\text{C}_{chiplev.}$		1,8		V
$V_{F0}$			1,1	1,2	V
	$T_j = 25 \text{ }^\circ\text{C}$				V
	$T_j = 125 \text{ }^\circ\text{C}$				V
$r_F$			9	13	V
	$T_j = 25 \text{ }^\circ\text{C}$				V
	$T_j = 125 \text{ }^\circ\text{C}$				V
$I_{RRM}$	$I_{Fnom} = 150 \text{ A}$		86		A
$Q_{rr}$	$di/dt = 2200 \text{ A}/\mu\text{s}$		17		μC
$E_{off}$	$V_{GE} = -15 \text{ V}; V_{CC} = 600 \text{ V}$		5,8		mJ
$R_{th(j-c)FD}$	per diode			0,32	K/W
<b>Module</b>					
$L_{CE}$				30	nH
$R_{CC'+EE'}$	res., terminal-chip	$T_{case} = 25 \text{ }^\circ\text{C}$	0,75		mΩ
		$T_{case} = 125 \text{ }^\circ\text{C}$	1		mΩ
$R_{th(c-s)}$	per module			0,05	K/W
$M_s$	to heat sink M6		3	5	Nm
$M_t$	to terminals M5		2,5	5	Nm
w				160	g


This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.



GB

GAL



**SEMITRANS<sup>®</sup> 2**

## Trench IGBT Modules

**SKM 195GB126D**

**SKM 195GAL126D**

Preliminary Data


### Features

- Trench = Trenchgate technology
- $V_{CE(sat)}$  with positive temperature coefficient
- High short circuit capability, self limiting to  $6 \times I_C$

### Typical Applications







- AC inverter drives
- UPS
- Electronic welders







$Z_{th}$		Conditions	Values	Units
<b><math>Z_{th(j-c)I}</math></b>				
$R_{\theta j-c}$	$i = 1$		115	mk/W
$R_{\theta j-c}$	$i = 2$		34	mk/W
$R_{\theta j-c}$	$i = 3$		9	mk/W
$R_{\theta j-c}$	$i = 4$		2	mk/W
$\tau_{th(j-c)}$	$i = 1$		0,0493	s
$\tau_{th(j-c)}$	$i = 2$		0,0174	s
$\tau_{th(j-c)}$	$i = 3$		0,0012	s
$\tau_{th(j-c)}$	$i = 4$		0,0002	s
<b><math>Z_{th(j-c)D}</math></b>				
$R_{\theta j-c}$	$i = 1$		200	mk/W
$R_{\theta j-c}$	$i = 2$		90	mk/W
$R_{\theta j-c}$	$i = 3$		26	mk/W
$R_{\theta j-c}$	$i = 4$		4	mk/W
$\tau_{th(j-c)}$	$i = 1$		0,054	s
$\tau_{th(j-c)}$	$i = 2$		0,0089	s
$\tau_{th(j-c)}$	$i = 3$		0,001	s
$\tau_{th(j-c)}$	$i = 4$		0,08	s



GB

GAL






# SKM 195GB126D ...


UL Recognized  
File no. E 63 532

Dimensions in mm


CASED61



Case D 61



GB Case D61



GAL Case D 62