



Standard extruded heatsinks

<p>art. no.</p>	
<p>SK 65 ...</p>	<p>for cases SOT 32</p>
<p>please indicate: (optional)</p> <p>37.5 75 mm 1 x M 3; 2 x M 3</p>	
<p>art. no.</p>	
<p>SK 64 ...</p>	<p>for cases TO 220</p>
<p>please indicate: (optional)</p> <p>37.5 75 mm 1 x M 3; 2 x M 3</p>	
<p>art. no.</p>	
<p>SK 419 ...</p>	
<p>please indicate:</p> <p>75 1000 mm</p>	
<p>art. no.</p>	
<p>SK 183 ...</p>	
<p>please indicate: (optional)</p> <p>50 75 mm TO 3; CB</p>	

Mounting for TO 3 angle
 Order example
 Attachable heatsinks for TO-cases
 Heatsinks for DC/DC converter

→ A 121
 → A 21
 → A 91
 → A 109 - 110

Heatsink profile-overview
 Mica wafers
 Insulator sleeves
 Insulating clamping parts

→ A 13 - 16
 → E 11
 → E 41
 → E 35