

LED workstation lighting

Neutral white 4500 K

Version:

- High-quality, robust aluminium housing in elegant design
- Acrylic glass protective cover
- 3-m grey connection wire
- Maintenance-free LED technology
- more variants with a beam angle of 100° available on request

Advantage:

- Ultra-modern LED technology for low consumption
- Optimum heat transfer for long service life
- Continuous, bright and dazzle-free illumination of work surfaces
- Versatile application thanks to simple and flexible mounting on aluminium strut profiles with integrated T-slots (8 mm)
- **Ref. no. 162 and 165:** Using the wireless version, workstation lighting can be switched on and off or dimmed via a wireless button (required accessories no. 50239 166). This allows any number of lights to be controlled using a single button or various light clusters to be assigned to different buttons. The minimum range inside buildings is 30 m.



Art. no.	50239 164
Width	64 mm
Length	1004 mm
Surface	Powder-coated
Colour	Traffic white RAL 90 16

EAN-Code

4053625317431