

## Electronic torque testing device for workshops Sensotork

With calibration certificate



### Application:

For checking and adjusting torque wrenches for clockwise and anti-clockwise measurements.

### Execution:

- Possible to transfer data to a PC
- Measuring units: Nm, ft-lb, modes: Track, Peak Hold, First Peak

### Advantage:

- Compact design
- Easy to expand using replaceable measuring value transducers
- High degree of accuracy

### Delivery:

Measuring value transducer, display unit, power supply unit, fastening kit, square adapter



<b>Art. no.</b>	<b>52293 230</b>
<b>Brand</b>	STAHLWILLE
<b>Manufacturer Part Number</b>	96521082
<b>Min. torque</b>	25 Nm
<b>Max. torque</b>	1100 Nm
<b>Drive</b>	3/4 inch
<b>Min./max. torque</b>	25-1100 Nm
<b>Error limit (%)</b>	1 %
<b>Calibration certificate</b>	Yes
<b>Gross Weight</b>	10.800 kg
<b>Product Group</b>	531

### EAN

4018754181155