

Pump set F424 S-43/38 electrical

Completely ready for use with stainless steel suction pipe, pressure hose and pump nozzle



Application:

For pumping flammable liquids.

Execution:

- Collector motor F 460 Ex, 230 V, 50 Hz, 460 W, shockproof, suppressed
- Motor with undervoltage trip and continuous speed adjustment
- Set comes complete with stainless steel pump pipe set with no seals
- 2-m universal hose line DN 21, earth cable 2 m
- Brass hose connections and pump nozzle

Advantage:

- Explosion-protected, built and approved in accordance with ATEX directive 94/9/EC category 2



Art. no.	56359 530
Brand	FLUX
Manufacturer Part Number	10-46024010
Model	F424 S-43/38
Max. immersion depth	1000 mm
Max. delivery height	9.5 m
Feed quantity	200 l/min
Suitable for container	60-200 litres
Max. temperature resistance	100 °C
Gross Weight	15.000 kg
Product Group	575

EAN

4260387213226