




**Data sheet | Item number: 2116-5207**

2-conductor ground terminal block; 16 mm<sup>2</sup>; with test port; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®



[www.wago.com/2116-5207](http://www.wago.com/2116-5207)



**Item description**

**Safety information 1:**

DIN 35 rails, height 15 mm, must be used if the current load is higher than 76A!

**Data**

**Connection data**

Connection technology

Push-in CAGE CLAMP®



|                                      |   |
|--------------------------------------|---|
| Actuation type                       | Push-in<br>Lever<br>Push-button           |
| Actuation type 2                     | Push-in<br>Push-button<br>Operating tool  |
| Connectable conductor materials      | Copper                                    |
| Nominal cross section                | 16 mm <sup>2</sup>                        |
| Solid conductor                      | 0.5 ... 16 mm <sup>2</sup> / 20 ... 6 AWG |
| Solid conductor, push-in termination | 2.5 ... 16 mm <sup>2</sup> / 14 ... 6 AWG |
| Fine-stranded conductor              | 0.5 ... 25 mm <sup>2</sup> / 20 ... 4 AWG |
| Strip length                         | 18 ... 20 mm / 0.71 ... 0.79 inch         |
| Total number of connection points    | 2   |
| Total number of potentials           | 1   |
| Number of levels                     | 1   |
| Type of wiring                       | Front-entry wiring                        |

### Geometrical Data

|                                       |                      |
|---------------------------------------|----------------------|
| Width                                 | 12 mm / 0.472 inch   |
| Height from upper-edge of DIN-35 rail | 37.1 mm / 1.461 inch |
| Depth                                 | 91.5 mm / 3.602 inch |

### Mechanical data

|                  |                     |
|------------------|---------------------|
| Design           | horizontal          |
| Type of mounting | DIN-35 rail         |
| Marking level    | Center/side marking |

### Material Data

|                     |                      |
|---------------------|----------------------|
| Color               | green-yellow         |
| Insulating material | Polyamide 66 (PA 66) |
| Fire load           | 0 MJ                 |
| Weight              | 40.159 g             |

### Commercial data

|                    |               |
|--------------------|---------------|
| Country of origin  | DE            |
| GTIN               | 4055143754453 |
| Customs Tariff No. | 85369010000   |




### Approvals / Certificates

Ex-Approvals



Certificate

| Logo   | Approval  | Additional Approval Text | name                  |
|--|---|--------------------------|-----------------------|
|  | AEx<br>UL International Germany GmbH c/o Physikalisch<br>Technische Bundesanstalt | UL 60079                 | E185892               |
|  | ATEX<br>Physikalisch Technische Bundesanstalt                                     | EN 60079-0               | PTB ATEX<br>1012 U    |
|  | IECEX<br>Physikalisch Technische Bundesanstalt                                    | IEC 60079-0              | IECEX PTB<br>18.0019U |

## Country specific Approvals

| Logo   | Approval                              | Additional Approval Text | Certificate name |
|--|---------------------------------------|--------------------------|------------------|
|    | CCA<br>DEKRA Certification B.V.       | EN 60947                 | NTR NL<br>7675   |
|   | CSA<br>DEKRA Certification B.V.       | C22.2                    | 70175104         |
|  | KEMA/KEUR<br>DEKRA Certification B.V. | EN 60947                 | 71-<br>103140    |

## UL-Approvals

| Logo   | Approval                                | Additional Approval Text | Certificate name |
|--|---|--------------------------|------------------|
|  | cURus<br>Underwriters Laboratories Inc. | UL 1059                  | E45172           |
|  | cURus<br>Underwriters Laboratories Inc. | UL 1059                  | E45172           |

## Downloads

## Documentation

## Bid Text

2116-5207

docx

[Download](#)



14.9 kB

---

## CAD/CAE - Smart Data

### CAD data

3D Download 2116-5207

URL

Download

---

Subject to changes.