



Halogen non-reflector

7023 100W GY6.35 12V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

General information					
Cap-Base	GY6.35 [GY6.35]				
Philips Code	7023				
ANSI Code	FCR				
LIF Code	A1/215				
Operating Position	S90 [Standing +/-90D or Base Down				
	(BDH)]				
Main Application	Projection				
Life to 50% Failures (Nom)	50 h				
Light technical					
Luminous Flux (Rated) (Nom)	3600 lm				
Correlated Color Temperature (Nom)	3450 K				
Color Rendering Index (Nom)	100				
Operating and electrical					
Power (Nom)	100 W				


Voltage (Nom)	12 V			
Mechanical and housing				
Bulb Material	Quartz-UV Open			
Filament Shape	Flat			
Filament Dimensions WxH	4.2x2.3			
Luminaire design requirements				
Bulb Temperature (Max)	900 ℃			
Pinch Temperature (Max)	400 °C			
Pinch Temperature (Max)-DUP(do not use) 400 °C				
Product data				
Full product code	871150040981250			
Order product name	7023 100W GY6.35 12V 1CT/10X10F			
EAN/UPC - Product	8711500409812			
Order code	923870017103			
Numerator - Quantity Per Pack	1			

Datasheet, 2022, September 12 data subject to change

Halogen non-reflector

Local code description	LAMPADA DE PROJECAO
Numerator - Packs per outer box	100
Material Nr. (12NC)	923870017103

Dimensional drawing



7023 100W GY6.35 12V 1CT/10X10F

Product	D (max)	L (min)	L (max)	L	P (max)	Р	P (min)	C (max)
7023 100W	11.5 mm	29.75	30.25	30	1.30 mm	1.25	1.20	44 mm
GY6.35 12V		mm	mm	mm		mm	mm	
1CT/10X10F								

