

High-performance drill, VariDrill solid carbide TiAlN VDS402A 5xD with IC HA

For universal use up to 1300 N/mm²

WIDIA 

Application:

For HPC boring up to a strength of 1300 N/mm²



Execution:

- High-performance solid carbide drill TiAlN WU25PD
- No drill heels
- Special grinding
- 30° spiral angle
- Straight main cutting edge

Advantage:

- design of VariDrill drill tip: long service life in almost all materials and fewer breakages at the cutting edge
- version without drill heel: uniform distribution of cutting forces leads to fewer breakages at the cutting edge
- design of VariDrill chip flute geometry: unhindered chip flow and problem-free chip removal

| | |
|---|-------------------|
| Art. no. | 19264 091 |
| Cutting edge diameter | 9.1 mm |
| Brand | WIDIA |
| Manufacturer Part Number | 4143091 |
| Tolerance of cutting edge diameter | m7 |
| Cutting material | SC |
| Surface | TiAlN |
| Max. drilling depth (D) | 5xD |
| Type | HPC UNI |
| Coolant supply | Internal |
| Tool holding device | HA parallel shank |
| Angle of the tip | 140 Degree |
| Shank diameter | 10 mm |
| Chip flute length | 61 mm |
| Length | 103 mm |
| f steel 1000 | 0.28 mm/r |
| Gross Weight | 0.078 kg |
| Product Group | 1XE |

EAN

4021169563539