

Tool cabinet with shelves

Doors optionally with perforated panel, slotted panel or viewing window

RasterPlan

Application:

For secure and clearly-arranged storage of high-quality tools.

Execution:

- Welded sheet steel frame with perforated rear wall throughout with 10 x 10 mm perforation grid, for attaching support elements
- Overlay double-walled, twist-resistant hinged doors, opening angle over 200°
- Doors lockable with bascule lock engaging on 3 sides



Art. no.	50639 111
Brand	RASTERPLAN
Manufacturer Part Number	1331.00.4016
Door design	Slotted plates
Width	1000 mm
Depth	410 mm
Height	1000 mm
With partition wall	No
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Colour of front	Gentian blue RAL 50 10
Surface	Lacquered
Cabinet colour	Light grey RAL 7035
Gross Weight	40.000 kg
Product Group	5AC

EAN

4251142200490