
## **KEMET Part Number: PME264NE5680MR30**

(P264EJ683M660A)



PME264/P264, Film, Metallized Paper, Safety, 0.068 uF, 20%, 660 VAC (X2), 1500 VDC, 85°C, Lead Spacing = 25.4mm



General Information	
PME264/P264	
Metallized Paper	
Radial	
EMI Safety	
Yes	
Wire Leads	
ENEC, UL, cUL	
No	
Molded	

Dimensions		
L	30.5mm MAX	
Н	19mm MAX	
Т	12.1mm MAX	
S	25.4mm +/-0.4mm	
LL	30mm +5mm	
F	1mm NOM	

Specifications	
Capacitance:	0.068 uF
Capacitance Tolerance:	20%
Voltage AC:	660 VAC (X2)
Voltage DC:	1500 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Dissipation Factor:	1.30% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	1000 V/us
Safety Class:	X2

Packaging Specifications		
Packaging:	Bulk, Bag	
Packaging Quantity:	100	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

