

# SSP1D412BDT

Solid state panel mount relay, 12 A, DC switching, thermal pad, input 3.5...32 V DC, output 1...150 V DC



## Main

|                                 |                               |
|---------------------------------|-------------------------------|
| Range of product                | Harmony Relay                 |
| Product or component type       | Solid state relay             |
| Provided accessory              | Thermal pad                   |
| Device short name               | SSP1                          |
| Mounting support                | Panel                         |
| Number of phases                | 1 phase                       |
| Contacts type and configuration | 1 NO                          |
| Line Rated Current              | 12 A                          |
| Solid state output type         | DC switching<br>Mosfet output |

## Complementary

|  |   |
|--|---|
| [Uc] control circuit voltage           | 3.5...32 V DC   |
| Minimum switching voltage              | 3.5 V DC turn-on  |
| Maximum switching voltage              | 1 V DC turn-off   |
| Response time                          | 0.1 ms turn-on)<br>0.1 ms turn-off)   |
| Input current                          | 10...15 mA  |
| Output voltage                         | 1...150 V DC  |
| Load current                           | 0.001...12 A  |
| Surge current                          | 31 A 10 ms  |
| Co-ordination type                     | Type 1 - 10 A miniature circuit breaker (MCB) B<br>Type 2 - 6 A miniature circuit breaker (MCB) B   |
| Maximum leakage current                | 0.3 mA off-state  |
| Maximum voltage drop                   | <2.8 V on-state   |
| Insulation resistance                  | 1000 MOhm 500 V DC  |
| Maximum capacitance                    | 50 pF input/output  |
| Dielectric strength                    | 2.5 kV AC input/output<br>2.5 kV AC input or output to case   |
| [Uimp] rated impulse withstand voltage | 2.5 kV output to case   |
| Tightening torque                      | 1.5...1.7 N.m input<br>2...2.2 N.m output   |
| Connections - terminals                | Screw terminals 0.2...3.3 mm <sup>2</sup> , AWG 24...AWG 12) with cable end input<br>Screw terminals 0.5...5.26 mm <sup>2</sup> , AWG 20...AWG 10) with cable end output<br>Screw terminals 0.2...3.3 mm <sup>2</sup> , AWG 24...AWG 12) without cable end input<br>Screw terminals 0.5...8.26 mm <sup>2</sup> , AWG 20...AWG 8) without cable end output<br>Forked type tag connectors 9.2 x 4 mm input<br>Ring lugs 9.2 x 4 mm input<br>Forked type tag connectors 11.7 x 4.5 mm output<br>Ring lugs 11.7 x 4.5 mm output |
| Thermal resistance                     | 0.71 °C/W junction to case  |
| Thermal pad impedance                  | 0.48 °C-in <sup>2</sup> /W at 25 psi  |
| LED indicator                          | LED, green input  |
| IP degree of protection                | IP20  |
| Safety reliability data                | MTTFd = 1875.9 years<br>B10d = 1731395  |
| Net Weight                             | 3.15 oz (89.2 g)  |
| Device presentation                    | Complete product  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

|                                       |  |
|---------------------------------------|--|
| Ambient air temperature for operation | -40...176 °F (-40...80 °C)                                     |
| Ambient air temperature for storage   | -40...257 °F (-40...125 °C)                                    |
| Pollution degree                      | 2  |
| Overvoltage category                  | III  |
| Product certifications                | CE<br>UL<br>EAC<br>CSA<br>RoHS                                 |
| Marking                               | CE<br>UL<br>EAC<br>CSA   |
| Standards                             | EN/IEC 62314<br>UL 508<br>EN/IEC 60950-1<br>CSA C22.2 No 14-13 |

## Ordering and shipping details

|                       |                                   |
|-----------------------|-----------------------------------|
| Category              | 22375 - INTERFACE MODULE(ABA,R,S) |
| Discount Schedule     | CP2                               |
| GTIN                  | 00785901774112                    |
| Nbr. of units in pkg. | 1                                 |
| Package weight(Lbs)   | 0.21 lb(US) (0.10 kg)             |
| Returnability         | Yes                               |
| Country of origin     | MX                                |

## Packing Units

|                  |          |
|------------------|----------|
| Package 1 Height | 0.380 dm |
| Package 1 width  | 0.480 dm |
| Package 1 Length | 0.650 dm |

## Offer Sustainability


|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | <a href="#">End Of Life Information</a>   |

Dimensions



- (1) Front view
- (2) Side view
- (3) Bottom view

Derating Curves



- A : Load Current (Arms)
- B : Ambient Temperature (°C)
- (1) For Heatsink SSRHP25
- (2) No Heatsink