

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Platinum Resistance Pt100 Class B Sensors with Teflon® Insulated lead in a Stainless Steel Tube



Quality & Service

About Labfacility

Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Formed in 1971, Labfacility specialize in the field of Temperature and Process

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Pt100 element to IEC 751 Class B
- 4 wire configuration
- Temperature range -50°C to + 200°C
- Pt100 element in a 3.0 or 4.0mm diameter 316 stainless steel probe
- 1 metre Teflon® insulated twisted lead, 4 core

Specifications

Sensor type: Pt100 (100 Ohms @ 0°C) to IEC 751, Class B

Construction: Insulated element in a 3.0 or 4.0mm diameter 316 stainless steel

probe

Probe temperature range: -50°C to +200°C

Extension cable: 1 metre Teflon® insulated 4 core twisted leads

Termination: 4-wire tails

Contact Details

Email sales@labfacility.com

Website
www.labfacility.com

Probe dimensions Product code (dia. x length)		order code
3mm x 100mm	RAA-S4B-3.0-100-NP-1.0-C5-T	XF-1107-FAR
4mm x 25mm 4mm x 40mm	RAA-S4B-4.0-25-NP-1.0-C5-T RAA-S4B-4.0-40-NP-1.0-C5-T	XF-1139-FAR XF-1140-FAR

