Inductor



RoHS Compliant



Specifications:

Inductance : 2.2µH Inductance Tolerance : ± 20% DC Resistance Max : 0.041Ω DC Current Rating : 3.8A : SMD Inductor Case Style No. of Pins Lead Spacing : 2mm Core Material : Ferrite External Depth : 5.2mm External Length / Height : 4.5mm External Width : 5.8mm Resonant Frequency : 100kHz Series : MCSD54

Electrical Characteristics (at 25°C)

100kHz 0.25V	L	2.2µH ±10%
at 25°C	DCR	41mΩ (Max.)
100kHz 0.25V Irms = 5.66A	ΔΤ	Temperature Rise 40°C (Max.)

Operating temperature: -55°C to +130°C

Material List


No.	Item	Material Description
1	Core	R5A CDR4.5 × 3.2(ST) B2 F1.5
2	Wire	Ø0.35mm × 1P 2UEWF 155°C
3	Solder (Lead Free)	Sn99.3%/Cu0.7%

Page <1>

Inductor




Schematic Diagram




Note:

- 1. Wire Ø0.35mm × 1P 2UEWF 155°C
- 2. 9.5TS (Reference)

Electric Characteristics







Inductor



Configurations and Dimensions





Dimensions: Millimetres

А	5.2 ±0.3mm	-
В	5.8 ±0.3mm	-
С	4.5 ±0.35mm	-
D	2mm	(Reference)
E	5.8 ±0.5mm	-

Part Number Table

Description	Part Number
Inductor, 2.2µH, 3.8A, 20%	MCSD54-2R2MU

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

