Signal Relay





Features:

Microminiature relay

• Dimension : 20.3 × 9.9 × 11.4 (mm)

High sensitivity

• 2 form contacts: 2 form C

Specifications:

Contact Data

Contact Material		AuAg overlay, Ag Alloy	
Con	tact Rating	1A 120V AC / 24V DC	
Con	lact Rating	2A 120V AC / 24V DC	
Contact Resistance		Max. 50mΩ (6V DC 0.1A)	
	Max. Switching Voltage	125V AC / 30V DC	
Load	Max. Switching Current	2A	
Load	Max. Switching Power	250VA,60W	
	Min. Switching Load	5V DC,10mA	
Life	Electrical	100,000 Operations	
Lile	Mechanical	15,000,000 Operations	

Coil Data

Name of Oak Dance	00014/
Nominal Coll Power	200mvv

General Data

Insulation Resistance		Min. 1,000MΩ 500V DC		
	Between Open Contacts	500V AC,1 Min		
Dielectric Strength	Between Coil and Contacts	1,000V AC,1 Min		
Оре	erate Time	Max. 7ms		
Rel	ease Time	Max. 3ms		
Operating Temperature		-25°C to +70°C		
Humidity		35 to 95% RH, +40°C		
Surge Strength		1,500V AC,10 × 160µs		
01 1 1 1 1 1	Endurance	1,000m/s ²		
Shock Resistance	Misoperation	100m/s ²		
Vibration Resist- ance	Endurance	10 to 55Hz 1 5mm Double Amplitude		
	Misoperation	10 to 55Hz, 1.5mm Double Amplitude		

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




Signal Relay





Coil Data:

Nominal Voltage V DC	Coil Resistance Ω ±10%	Operate Voltage ≤ V DC	Release Voltage ≥ V DC	Coil Power mW	Part Number	
5	55.6	3.75	0.5	200	MC25134	ĺ

Out Line, Wiring Diagram, Mounting Hole Layout









Dimensions: Millimetres

Characteristic Chart Data

Timing



Coil Temperature Rise




Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




Signal Relay

multicomp PRO

Life Curves



Maximum Switching Power



Part Number Table

Description	Part Number
Signal Relay, 5 VDC, DPDT, 2A, Through Hole	MC25134

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

