

# uvex

## Latest hand protection solutions from uvex

uvex offer a wide range of safety gloves, suitable for a variety of applications. We pay particular attention to the fit and feel of the glove, as we know if your PPE isn't comfortable, it won't get worn. In addition to the uvex core range of products, uvex is partnered with HexArmor®, offering a wide range of unique and complementary solutions that combat industrial ultra-high cut, puncture, needlestick and impact injuries. Take a look at our latest glove solutions:

### uvex unilite7710F


The uvex unilite 7710F is a fully coated multi-purpose safety glove for a variety of heavy-duty tasks. With a seamless 15 gauge Nylon liner, the uvex unilite 7710F provides excellent dexterity and comfort. The full flat nitrile base coating provides protection against moisture and water reaching the skin, keeping hands dry.

- Fully coated safety glove with grip finish suitable for wet and oily applications
- The model ensures that no moisture reaches the skin from the outside
- EN407 Level 1 – 100° heat protection – ideal for low risk contact hot handling
- Extended knitted cuff, assists with keeping dirt out of the glove
- Level 4 Abrasion resistance, extremely durable for longevity of use

Sizes 7 to 11




Product number 60278

EN388:2016	Abrasion resistance (0-4)	4
 <b>4121X</b>	Cut resistance (0-5, X not applicable)	1
	Tear resistance (0-4)	2
	Puncture resistance (0-4)	1
	Cut resistance (ISO A-F)	X
	EN407	Resistance to contact heat
<b>X1XXXX</b>		

### HexArmor Helix® 2065



Product number 2065

EN388:2016	Abrasion resistance (0-4)	4
 <b>4X42D</b>	Cut resistance (0-5, X not applicable)	X
	Tear resistance (0-4)	4
	Puncture resistance (0-4)	2
	Cut resistance (ISO A-F)	D
	<b>ANSI/ISEA CUT A3</b>	

Sizes 5 to 12

Helix® series gloves offer a wide variety of grip options to provide users with the appropriate grip for the task at hand. Helix gloves are manufactured in a seamless knitting machine, producing a close-fitting 13-gauge glove. The higher the gauge, the thinner, more dexterous, and comfortable the glove can be.

- Full flat nitrile coating offers 360° of water resistance and ANSI/ISEA level A3 cut protection
- 13-gauge HPPE, fibreglass, and nylon blend shell for enhanced comfort and breathability
- Flexible sandy nitrile palm coating provides superior grip and abrasion resistance
- Knit wrist helps prevent dirt and debris from entering the glove
- Launderable for extended life

### HexArmor Helix® 2076


Innovation intertwined with safety. Helix® Series gloves are tightly knit with strong yet extremely dexterous fibers that offer industry leading cut protection and abrasion resistance. A seamless series that answers the call of duty for most jobs, these high-comfort knit gloves feature consistent sizing and fit.

- Innovative 13-gauge HPPE and steel fibre blend shell offering 360° degree cut protection
- Knit wrist helps prevent dirt and debris from entering the glove
- Flexible polyurethane palm coating provides superior grip and abrasion resistance
- Reinforced thumb crotch area for increased durability
- Dry, oil or wet duty

Sizes 6 to 11



Product number 2076

EN388:2016	Abrasion resistance (0-4)	4
 <b>4X44F</b>	Cut resistance (0-5, X not applicable)	X
	Tear resistance (0-4)	4
	Puncture resistance (0-4)	4
	Cut resistance (ISO A-F)	F
	<b>ANSI/ISEA CUT A6</b>	