

## SDNC clamp holder for lathes, neutral

For longitudinal and copy turning using DC indexable inserts

**ATORN**<sup>®</sup>

### Application

For longitudinal and copy turning using DC 55° indexable inserts



### Version

- Precision-made steel support, bronzed, hardened, type D, pitch angle 62.5°, tip angle 55°, clearance angle 7°

<b>Art. no.</b>	<b>17829 061</b>
<b>ISO name</b>	SDNC N 1212 X11-A
<b>Shaft height</b>	12 mm
<b>Shank width</b>	12 mm
<b>Length</b>	130 mm
<b>Programming size</b>	12 mm
<b>Suitable for indexable inserts</b>	DC.. 11T3..
<b>Tool design</b>	Neutral
<b>DIN</b>	4983

### EAN-Code

4050293692907