

Hinged-door cabinet housing with solid sheet metal doors, height 1950 mm and fixed built-in partition

Cabinet housing without internal configuration

Application:

For customised configuration with drawers and shelves, for secure and clearly-visible storage of tools, accessories, files or many other parts.

Execution:

- Housing of welded sheet steel structure
- Doors edged and reinforced
- Safety lock for secure locking of the cabinets
- Rails plugged in to enable rapid conversion
- Grid system: Shelves and drawers adjustable in 30:30 mm increments
- Can be optionally equipped with: Drawers with front height 90 and 150 mm, full extension, load capacity 50 kg, width x depth 386 x 395 mm, see no. 50053 600-615
- Fixed or pull-out shelves, see no. 50053 620-635
- cabinet can be fitted with an ELECTRONIC CODE combination lock at extra charge as an option, see no. 50392 020



Art. no.	50053 450
Brand	HK
Manufacturer Part Number	50053450
Door design	Full-sheet panel
Height	1950 mm
Width	1000 mm
Depth	500 mm
Effective height	1840 mm
Load-carrying capacity	500 kg
With doors	Yes
With partition wall	Yes
Central locking	Yes
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Gentian blue RAL 5010
Surface	Powder-coated
Gross Weight	75.000 kg
Product Group	501

EAN

4039247469604