

Solid carbide end mill

4 flutes, TiAlN-coated

ORION[®]

Application:

End mill for universal processing.

Execution:

- Solid carbide ultra-fine grain
- Up to Ø 5 mm straight shank in line with DIN 6535 HA
- From Ø 6 mm straight shank in line with DIN 6535 HB
- TiAlN-coated
- Centre cutting
- Short version
- Very high feed rates possible



Art. no.	16837 320
Brand	ORION
Manufacturer Part Number	16837320
Cutting material	SC
Surface	TiAlN
Type	H
Number of cutting edges	4 PCS
Twist angle	30°
Tool holding device	HB parallel shank
Construction length	Short
Cutting edge diameter	20 mm
Cutting edge length	25 mm
Length	82 mm
Shank diameter	20 mm
fz steel 1000	0.17 mm
Gross Weight	0.200 kg
Overall stainless steel suitability	3
fitness not iron total	3
fitness Titan/Nickel/Super total	3
Product Group	150

EAN

4039247575336