


## Data Sheet

**Type Number** ..... 321  
**Designation IEC** ..... SR 65  
**System** ..... Silver oxide / Zinc /  
 Alkaline - Electrolyte



**Nominal Voltage** ..... 1,55 V  
**Typical Capacity C** ..... 14,5 mAh  
 Load 68,1 kOhm, at 20°C down to 1.2 V

**Weight (approx.)** ..... 0,25 g  
**Volume** ..... 0,06 ccm  
**Coding**..... Date of Manufacturing  
 Month/Year

**Temperature Ranges** min max.  
 Storage ..... 0°C 60°C  
 Discharge ..... 0°C 60°C

**Dimensions** min max.  
 Diameter (Ø)..... 6,65 6,80  
 Height (A/B) ..... 1,47 1,65

**Segment** ..... Watch

**Main Applications** ..... Watch  
 Electronic

### Typical Capacities (at 20°C)

| Discharge Type                             | Load              | End Voltage:    | 1.2 V |
|--|-------------------|-----------------|-------|
| Continuous<br>24h/d, 7d/w<br>Current [µA]: | 68100 Ω<br><br>23 | Time:           | 630 h |
|  |                   | Capacity [mAh]: | 14,5  |
|  |                   | Energy [mWh]:   | 22,5  |