




INCL. CONTROLLER SSD1803A FOR 4-/8-BIT, SPI AND I²C



TECHNICAL DATA

- * HIGH-CONTRAST LCD SUPERTWIST DISPLAY
- * OPTIONAL LED BACKLIGHT UNITS IN DIFFERENT COLORS
- * 4x20 CHARACTER WITH 4.8 mm HEIGHT
- * SSD1803A CONTROLLER FOR 4-/8-BIT, SPI (2-/3-/4-WIRE) AND I²C (2-WIRE) INTERFACE
- * SINGLE POWER SUPPLY +3.3V (typically 250µA)
- * NO ADDITIONAL VOLTAGES REQUIRED
- * OPERATING TEMPERATURE RANGE -20 THROUGH +70°C
- * LED BACKLIGHT 3 through 80mA@3.3V or 2 through 40mA@5V
- * NO MOUNTING REQUIRED, SIMPLY SOLDER INTO PCB
- * 3 DIFFERENT CHARACTER SETS (CYRILLIC, ENGLISH-JAPANESE AND EUROPEAN) INCLUDED IN THE SAME CONTROLLER
- * 2 VIEWING DIRECTION POSSIBLE (BOTTOM AND TOP VIEW)

ORDERING CODE

<pre>LCD MODULE 4x20 - 4.8 mm x: B = blue background W = white background transfelctive S = black background</pre>	EA DOGM204x-A
N = white background reflective LED BACKLIGHT, WHITE LED BACKLIGHT, AMBER LED BACKLIGHT, GREEN/RED	EA LED66X40-W EA LED66X40-A EA LED66X40-GR
USB TEST BOARD FOR PC (WINDOWS) SOCKET CONNECTOR 4.8 mm HIGH (1x22-PIN, 2.54mm PITCH)	EA 9780-3USB EA FL-22P



EA DOG SERIES

With its EA DOG series, ELECTRONIC ASSEMBLY presents the world's first display series which will run on 3.3 V systems without auxiliary power.

Unlike normal LCD modules, you order the display and the corresponding backlight separately. This gives you a wealth of possible combinations.

Designed for compact hand-held devices, this modern LCD range provides a number of real benefits with or without backlight:

- * extremely compact at 66 x 40 mm at the standard font size of 4.8 mm (4 x 10)
- * ultra-flat at 2.0 mm without backlight or 5.8 mm including LED backlight
- * 4-bit, 8-bit, SPI interface (2-/3-/4-wire) and I²C (2-wire)
- * typical power consumption of only 250µA in full operation (LED white backlight as of 3mA)
- * easy installation by simply soldering into the board
- * A whole range of design variants can be supplied as of single units
- * Changing background color

LED BACKLIGHTS

5 different variants are available for individual backlighting: white, yellow/green, red, amber and bicolor.

For monochrome backlights, 2 separate LED paths are available, which can be switched in parallel or in series to ideally match the system voltage. This means that all the backlights can be run either at 3.3 V and higher voltages.

Operation of the backlight requires an external series resistor for current limiting. This can be calculated by R=U/I; you will find the values in the table. To improve life time it is recommanded to use a current source only.

The operating life of the yellow/green, red and amber backlights is 100,000 hours and that of the white backlight is a bit shorter.

Important: Never operate the backlight directly on a 5 V/3.3V supply, as this can immediately destroy the LEDs!

amber	Forward	Current	Limiting resistor			
EA LED66x40-A	voltage	max.	@ 3,3 V	@ 5 V		
Connected in parallel	2,1 V	72 mA	18 ohm	47 ohm		
Connected in series	6,3 V	24 mA	-	-		

white	Forward	Current	Limiting resistor			
EA LED66x40-W	voltage	max.	@ 3,3 V	@ 5 V		
Connected in parallel	3,2 V	90 mA	1,2 ohm	24 ohm		
Connected in series	9,6 V	30 mA	-	-		

green/red	Forward	Current	Limiting	resistor
EA LED66x40-GR	voltage	max.	@ 3,3 V	@ 5 V
red path (ARG/CR)	2,1 V	80 mA	24 ohm	48 ohm
green path (ARG/CG)	2,1 V	80 mA	18 ohm	39 ohm

INSTALLATION

First, the display and the corresponding backlight are clipped together. The complete unit is then inserted into a PCB and soldered. Note that the 4 pins for the backlight must also be soldered from the top with less tin.

<u>Important:</u> There are one or two protective films on the display (top and/or rear side) and one on each backlight. Those have to be removed during or after production.




4 DIFFERENT TECHNOLOGIES

As a standard we provide 4 different technologies as STN and FSTN:

display type	technology	optional backlight	readability	display color non backlighted	display color with backlighted	recommende backlight color
EA DOGM204W-A FSTN positiv white LED transflective	FSTN pos. transflective	it's fine with and without backlight	readable even without backlight	black on white	black on backlight color	white, blue, RGB
EA DOGM204B-A STN negativ blue white LED transmissive	STN neg. blue transmissive	usage only with backlight			backlight color on blue background	white, yellow/green
EA DOGM2048-A FSTN negativ white LED transmissive	FSTN neg. transmissive	usage only with backlight			backlight color on black background	white, RGB
EA DOGM204N-A FSTN positiv reflective no backlight	FSTN pos. white reflective	no backlight possible	finest readable without backlight	black on white		

3 DIFFERENT BACKLIGHTS

3 different backlight colors are available to match equipments design as much as possible. The most effective and brightest one is the white one EA LED66x40-W.



When you can see black and white pictures only here on this page then you're able to download a coloured version from our website <u>http://www.lcd-module.de/eng/pdf/doma/dogm204e.pdf</u>

USB-TEST BOARD EA 9780-3USB

For easy startup, a USB test board is available that can be connected to a PC. An USB cable and a Windows software is supplied with the product. This allows individual text and to be displayed directly on the connected display.

SIMULATION WITH WINDOWS


Without ordering a display, the simulator software may show all the displays and colors even without the hardware. You can download for free from our website. There's no need to install, it's a simple EXE file, also running from USB stick e.g. <u>http://www.lcd-module.de/deu/disk/startdog_V33.zip</u>




APPLICATION EXAMPLES

Different wiring must be used depending on the interface.

Note that the COG technology means that the current capacity of the outputs is limited. Therefore, a large load on the bus may cause signal loops and unclean levels. If in doubt, additional pull-down resistors (8051) are required or additional waits/NOPs must be incorporated.







INITIALISATION EXAMPLES

			Init	tializ	zati	on	Exa	Imp	ole 8	3-Bi	it, S	PI and I2C
Command	RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0	Hex	Remark
Function Set	0	0	0	0	1	1	1	0	1	0	\$3A	8 bit data length extension Bit RE=1; REV=0
Extended function set	0	0	0	0	0	0	1	0	0	1	\$09	4 line display
Entry mode set	0	0	0	0	0	0	0	1	1	0	\$06	bottom view
Bias setting	0	0	0	0	0	1	1	1	1	0	\$1E	BS1=1
Function Set	0	0	0	0	1	1	1	0	0	1	\$39	8 bit data length extension Bit RE=0; IS=1
Internal OSC	0	0	0	0	0	1	1	0	1	1	\$1B	BS0=1 -> Bias=1/6
Follower control	0	0	0	1	1	0	1	1	1	0	\$6E	Devider on and set value
Power control	0	0	0	1	0	1	0	1	1	1	\$57	Booster on and set contrast (DB1=C5, DB0=C4)
Contrast Set	0	0	0	1	1	1	0	0	1	0	\$72	Set contrast (DB3-DB0=C3-C0)
Function Set	0	0	0	0	1	1	1	0	0	0	\$38	8 bit data length extension Bit RE=0; IS=0
Display On	0	0	0	0	0	0	1	1	1	1	\$0F	Display on, cursor on, blink on

			In	itia	liza	tior	ı Ex	ample 4-Bit
Command	RS	R/W	DB7	DB6	DB5	DB4	Hex	Remark
Synchronize 1	0	0	0	0	1	1	\$33	Make sure to switch to 8 bit data length
Synchronize 2	0	0	0	0	1 1	1 0	\$32	Switch to 4 bit data length
Function Set	0	0	0	0	1	0	\$2A	4 bit data length extension Bit RE=1; REV=0
Extended funcion set	0	0	0	0	0	0	\$09	4 line display
Entry mode set	0	0	0	0	0	0	\$06	bottom view
Bias setting	0	0	0	0	0	1	\$1E	4 bit data length extension Bit RE=0; IS=1
Function Set	0	0	0	0	1	0	\$29	4 bit data length extension Bit RE=0; IS=1
Internal OSC	0	0	0	0	0	1	\$1B	4 bit data length extension Bit RE=0; IS=1
Follower control	0	0	0	1	1	0	\$6E	Devider on and set value
Power control	0	0	0	1	0	1	\$57	Booster on and set contrast (DB1=C5, DB0=C4)
Contrast Set	0	0	0	1 0	1	1 0	\$72	Set contrast (DB3-DB0=C3-C0)
Function Set	0	0	0	0	1 0	0	\$28	4 bit data length extension Bit RE=0; IS=0
Display on	0	0	0 1	0	0 1	0 1	\$0F	Display on, cursor on, blink on

12:00 VIEWING ANGLE, TOP VIEW OPTION

If the display is read mostly from above (on the front of a laboratory power supply unit, for example), the preferred angle of viewing can be set to 12 o'clock. This rotates the display by 180°. A slightly different initialization setup is required for this.

EA DOGM204x-A 4x20 characters 4.8mm height temperature -20..70

6 o'clock (Bottom View)

12 o'clock (Top View)



SETTING THE CONTRAST

The contrast for the EA DOGM204-A can be set by command. This is done using bits C0 through C5 in the commands "Contrast Set" and "Power/Icon

Control/Contrast Set". Generally, the contrast is set once only. Thanks to the integrated temperature compensation function it is kept constant allover the entire operating temperature range (-20 to $+70^{\circ}$ C).

						С	on	tras	st se	et (8	3-Bi	it)
Command	RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0	Hex	Remark
Function Set	0	0	0	0	1	1	1	0	0	1	\$39	8-Bit data length extension Bit RE=0; IS=1
Power control	0	0	0	1	0	1	0	1	1	1	\$57	Booster on and set contrast (DB1=C5, DB0=C4)
Contrast Set	0	0	0	1	1	1	0	0	1	0	\$72	Set contrast (DB3-DB0=C3-C0)
Function Set	0	0	0	0	1	1	1	0	1	0	\$38	8-Bit data length extension Bit RE=0; IS=0


Further information about the commands of the SSD1803A, please refer to the datasheet: http://www.lcd-module.de/fileadmin/eng/pdf/zubehoer/ssd1803a_2_0.pdf





CHARACTER SET

The controller has 3 built-in character sets. They can be selected with the command "ROM-Selection" in the extended command set.



	Change character table														
Command	ommand RS RW DB7 DB6 DB5 DB4 DB3 DB2 DB1 DB0 Hex Remark														
Function Set	0	0	0	0	1	1	1	0	1	0	\$3A	8-Bit data length extension Bit RE=1			
ROM Selection	0	0	0	0	0	0	1	0	0	1	\$72	ROM selection double byte command			
	1	0	0	0	0	0	R2	R1	0	0	\$0X	\$00 = ROMA; \$04=ROMB; \$0C=ROMC			
Function Set	0	0	0	0	1	1	1	0	0	0	\$38	8-Bit data length extension Bit RE=0			

Example code

CREATING YOUR OWN CHARACTERS

It's possible to create 8 own additional characters (ASCII Codes 0..7) to the fixes ROM codes

- 1.) The command "CG RAM Address Set" defines the ASCII code (Bit 3,4,5) and the dot line (Bit 0,1,2) of the new character. Example demonstrates creating ASCII code \$00.
- 2.) Doing 8 times the write command "Data Write" defines line by line the new character. 8th. byte stands for the cursor line.
- 3.) The new defined character can be used as a "normal" ASCII code (0..7); use with "DD RAM Address Set" and "Data Write".

		(Cha	irac	ter-	dat	a							
	Bit													
7	6	5	4	3	2	1	0	Hex						
			0	0	1	0	0	\$04						
			0	0	1	0	0	\$04						
			0	0	-	0	0	\$04						
v	х	v	0	0	-	0	0	\$04						
^	^	^	1	0	-	0	┯	\$15						
			0	1	1	T	0	\$0E						
			0	0	٦	0	0	\$04						
			0	0	0	0	0	\$00						

	Define own character												
Command	RS	R/W	DB7	DB6	DB5	DB4	DB3	DB2	DB1	DB0	Hex	Remark	
CG-RAM address set	0	0	0	1	AC5	AC4	АСЗ	AC2	AC1	AC0	\$40	Set address of character \$40=0; \$48=1; \$54=2\$78=7	
						0	0	1	0	0	\$04	first line	
						0	0	1	0	0	\$04	second line	
						0	0	1	0	0	\$04	third line	
Character-data	1	0	x	x	x	0	0	1	0	0	\$04	fourth line	
						1	0	1	0	1	\$15	fifth line	
						0	1	1	1	0	\$0E	sixth line	
						0	0	1	0	0	\$04	seventh line	
						0	0	0	0	0	\$00	eighth line, cursor line	



SERIAL INTERFACE (SPI)


The serial interface always needs a synchronization byte. In write mode, the byte to send hast to be devided in two bytes, into the "lower data" and "upper data". Please refer to the chart below. The maximum clock frequency for SCLK is 1 MHz.

SPI, 2-/3-WIRE

With 2 or 3 lines SCLK, SID and SOD (if necessary) the display EA DOGM204-A may be connected directly to the SPI interface of a μ C.


SPI, 4-WIRE

If there is more than one component connected to the SPI, an additional "Chipselect" line is required. For those you need to insert an AND-gate (e.g. 74HC1G08) with the SCLK line. On page 4 you do find an application example. Please mention that the logic for CS ist H-active.




I²C INTERFACE

The display can be assigned to the slave adress 0x78 or 0x7A (PIN SA0). After transfering the start condition, the hardware adress, togehter with the Read(1)/Write(0) bit has to be transmitted. While writing to the display, after the slave adress, there always is a control byte holding the information Data(1) or Command(0) and the continuation bit. If the continuation bit is set to 0, the following bytes are data bytes until the next stop condition occurs. The maximum clock rate for I²C bus is 400 kHz.



Further information about the interfaces and the timing of the SSD1803A, please refer to the datasheet http://www.lcd-module.de/fileadmin/eng/pdf/zubehoer/ssd1803a_2_0.pdf



ELECTRONIC ASSEMBLY GmbH Zeppelinstraße 19 D-82205 Gilching Germany
 Fon:
 +49 (0)8105-778090

 Fax:
 +49 (0)8105-778099

 e-Mail:
 info@lcd-module.de

 Web:
 www.lcd-module.com

