

**HANDLE SHANKS**

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, semi-matte finish.

**STANDARD EXECUTIONS**

- **RHUG-03**: back mounting, zinc-plated steel tapped bosses.
- **RHUG-04**: front mounting, pass-through holes for stainless steel cylindrical-head screws with hexagon socket and zinc-plated self-locking nuts, included in the supply.

Colour index:

- **01**: anodised aluminium tube, shaped, natural colour, matte finish.
- **04**: anodised aluminium tube, shaped, black colour, matte finish.

**FEATURES AND APPLICATIONS**




RH-UG series handles can be used in many different applications. The central aluminium tube, supplied separately from the shanks, is extremely simple and safe to assemble.

RH-UG series handles adapt well to use on a 19" rack and instruments in general.

HE = height unit of the front panel: 1 HE = 44.45 mm = 1 6/8".

**SPECIAL EXECUTIONS ON REQUEST**

Different lengths.



**RHUG-03**

Code	Code	f	L	d	p	B	h	l	li	G	HE*	⚖
RHUG-03.055.01	RHUG-03.055.04	55	65	M5	12	9	40	12	15	88.1	2	40
RHUG-03.088.01	RHUG-03.088.04	88	98	M5	12	9	40	12	15	132.5	3	44
RHUG-03.100.01	RHUG-03.100.04	100	110	M5	12	9	40	12	15	132.5	3	45
RHUG-03.120.01	RHUG-03.120.04	120	130	M5	12	9	40	12	15	177	4	48
RHUG-03.180.01	RHUG-03.180.04	180	190	M5	12	9	40	12	15	221.5	5	56

**RHUG-04**

Code	Code	f	L	d	B	h	l	li	G	HE*	⚖
RHUG-04.055.01	RHUG-04.055.04	55	70	M5	9	40	12	15	88.1	2	40
RHUG-04.088.01	RHUG-04.088.04	88	103	M5	9	40	12	15	132.5	3	44
RHUG-04.100.01	RHUG-04.100.04	100	115	M5	9	40	12	15	132.5	3	48
RHUG-04.120.01	RHUG-04.120.04	120	135	M5	9	40	12	15	177	4	51
RHUG-04.180.01	RHUG-04.180.04	180	195	M5	9	40	12	15	221.5	5	59

HE\* = height unit of the front panel: 1 HE = 44.45 mm = 1 6/8".