

TM-PFX30 S47-G0 FOR POTENTIAL GROUP, WITH SUPPLY FROM LEFT FOR ROUTING U1 M SG1 TO 6 FOR EXTERNAL ET200S-STATION 30MM

General technical data:

Product designation		Terminal module
Product type designation		TM-PFX30 S47-G0 for PM-D F X1
Design of the product		for PMD-F X1 modules with infeed from left
Mounting height	mm	196.5
Installation width	mm	30
Installation depth	mm	102
Protection class IP		IP20
Insulation voltage Rated value	V	500
Operating voltage		
• for DC Rated value	V	24
Operating current Rated value	A	10
Type of connectable conductor cross-section		
• solid		1x (0.14 ... 2.5 mm ²)
• finely stranded with core end processing		1x (0.14 ... 1.5 mm ²), acc. to IEC 60947
• for AWG conductors		
— solid		1x (18 ... 22)
— stranded		1x (18 ... 22)

Installation/ mounting/ dimensions:

Size of the screwdriver tip		Standard screwdriver Size 1
Tightening torque with screw-type terminals	N·m	0.4 ... 0.7

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK19033AE10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RK19033AE10/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK19033AE10&lang=en>

last modified:

15.01.2015