

Miniature cutting insert type AI HC5640

For thread cutting 60°

ATORN[®]

Application

For thread cutting 60° in steel and (stainless steel) material groups at low to high cutting speeds and mid-range cutting conditions.

Version

- Solid carbide cutting insert 60° with internal cooling

Advantage

- Robust cemented carbide grade for a broad application range
- Stable geometry optimised for female thread cutting machining
- Ideal for use with low-performance machines and unstable cutting conditions



Art. no.	17124 214
ISO name	AI
Shaft diameter	6 mm
Edge angle	60 Degree
Length	51 mm
Clearance length	15 mm
Min./max. pitch	1.0-1.5 mm
Programming size	2.6 mm
Machining direction	Left
Carbide type	HC5640
Material to be processed	Stainless steel, Non-ferrous metal

EAN-Code

4050293375374