

## Indenter with test diamond 136° Vickers

HV28 >HV0.01, for stationary hardness testers

### Application:

Vickers indenter HV28  $\geq 0.01$  HV for e.g. QNESS macro/REICHERTER Briro UVN-/ EMCO-TEST macro hardness testers

<b>Art. no.</b>	<b>42215 621</b>
<b>Testing method</b>	Vickers
<b>Test body</b>	Diamond pyramid 136°
<b>Suitable for min. testing method</b>	HV 0,01
<b>Calibration certificate</b>	DAkkS calibration certificate according to DIN EN ISO, DAkkS calibration certificate according to ASTM
<b>Shank diameter</b>	6.35 mm
<b>Shaft length</b>	18 mm
<b>Connection thread</b>	M5
<b>Functional diameter indenter</b>	6.5 mm
<b>Functional length indenter</b>	28 mm
<b>Length indenter</b>	46 mm
<b>Width across flats</b>	9 mm
<b>Gross Weight</b>	0.200 kg
<b>Product Group</b>	427

