

[IMAGE]

Product Information

Product Category	MICROWAVES
Unit Barcode	5016368094228
Outer Carton Barcode	
Commodity Code	8516500000
Country of Origin	CHINA
Primary Colour	STAINLESS STEEL
Finish	PAINTED STEEL
Primary Material	PLASTIC
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

General Product Specification

Voltage	230
Frequency	50
Wattage	900
Rated Current	6
Fuse Rating	
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	1.01
Class	CLASS I
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	281	483	450
Packaged Dimensions H x W x D (mm)	362	564	480
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			16
Unit Packaged Weight (Kg)			18.1
Carton Weight (Kg)			
EPS (Kg)	0.5	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.021	Card / Paper (Kg)	1.45
Aluminium (Kg)		Steel (Kg)	

Category Specific Technical Information

Cavity Capacity	25	Freestanding or Built-in	FREESTANDING
Cavity Depth	360	Grill Function	YES
Cavity Height	197	Grill Output Power	
Cavity Material	STAINLESS STEEL	Housing Colour	SILVER
Cavity Width	340	Interior Light	YES
Control Panel Lock	YES	Inverter Technology	NO
Control Type	DIALS & BUTTONS	MAFF Rating	E
Convection Cooking Function	YES	Max Timer Value	
Convection Output Power		Microwave Output Power	900
Defrost Function	YES	Number of Auto Cooking Programmes	10
Digital Display	YES	Number of Microwave Power Levels	11
Door Hinge Position	LEFT	Turntable Diameter	270
Flatbed	NO	Turntable On/Off Function	