

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 16.05.2019

Version number 3

Revision: 16.05.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name: Stazon cleaner**
- **1.2 Relevant identified uses of the substance or mixture and uses advised against:**
No further relevant information available.
- **Application of the substance / the preparation:** Cleaner for stamp
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
TSUKINEKO CO., LTD.
5F SUEHIRO JF BLDG., 5-1-5, SOTOKANDA, CHIYODA-KU, TOKYO 101-0021 JAPAN
Phone number: +<81> 3-3834-1080 (Japan)
FAX number: +<81> 3-3834-1050 (Japan)
- **Further information obtainable from:** Sales department
- **1.4 Emergency telephone number:** Phone number: +<81> 3-3834-1080 (Japan)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
The product is not classified, according to the CLP regulation.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008** Void
- **Hazard pictograms** Void
- **Signal word** Void
- **Hazard statements** Void
- **Additional information:**
Contains 60 % of components with unknown hazards to the aquatic environment.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Chemical characterisation: Mixtures**
- **Description:** Mixture of substances listed below with nonhazardous additions.

· Dangerous components:		
CAS: 57-55-6 EINECS: 200-338-0	propylene glycol ⚠ Acute Tox. 4, H302	35-45%
CAS: 2517-43-3 EINECS: 219-741-8	3-methoxybutan-1-ol ⚠ Flam. Liq. 3, H226	10-20%
CAS: 100-51-6 EINECS: 202-859-9 Index number: 603-057-00-5	benzyl alcohol ⚠ Acute Tox. 4, H302; Acute Tox. 4, H312; Acute Tox. 4, H332	6-8%

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:**
Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.
In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:**
Remove contaminated clothing and shoes.

(Contd. on page 2)

EU

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 16.05.2019

Version number 3

Revision: 16.05.2019

Trade name: Stazon cleaner

(Contd. of page 1)

- Immediately rinse with water.
- If skin irritation continues, consult a doctor.
- **After eye contact:**
Rinse opened eyes for several minutes under running water.
If symptoms persist, consult a doctor.
- **After swallowing:**
Rinse out mouth with water.
If symptoms persist consult a doctor.
- **4.2 Most important symptoms and effects, both acute and delayed**
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
Carbon dioxide, dry chemical powder, alcohol resistant foam, dry sand, water spray
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture:**
Nitrogen oxides (NO_x)
Carbon monoxide (CO)
- **5.3 Advice for firefighters**
Use dry chemical powder, carbon dioxide, dry sand for early stage of fire.
Apply water from a safe distance to cool and protect surrounding area.
Remove containers to a safe place.
- **Protective equipment:**
Mouth respiratory protective device.
Wear fully protective suit.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:**
Do not allow product to reach sewage system or any water course.
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Open and handle receptacle with care.
Wear proper protective equipment to avoid contact and inhalation.
- **Information about fire - and explosion protection:** Keep respiratory protective device available.

(Contd. on page 3)

EU

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 16.05.2019

Version number 3

Revision: 16.05.2019

Trade name: Stazon cleaner

(Contd. of page 2)

- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Store away from oxidizing agents.
- **Further information about storage conditions:** Keep container tightly sealed.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
- **Respiratory protection:** Use suitable respiratory protective device in case of insufficient ventilation.
- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture. Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves:**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material:**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:**



Tightly sealed goggles

- **Body protection:**
Apron
Boots

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**
Form: Liquid

(Contd. on page 4)

EU

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 16.05.2019

Version number 3

Revision: 16.05.2019

Trade name: Stazon cleaner

(Contd. of page 3)

· Colour:	Clear
· Odour:	Slightly smell
· Change in condition	
Initial boiling point and boiling range:	Not determined
· Flash point:	64.5 °C
· Explosive properties:	Not determined.
· Vapour pressure:	Not determined.
· Density:	Not determined.
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with water:	Soluble
· Solvent content:	
VOC (EC)	100.00 %
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions:** Reacts with oxidising agents.
- **10.4 Conditions to avoid:** No further relevant information available.
- **10.5 Incompatible materials:** Oxidising agent
- **10.6 Hazardous decomposition products:**
Nitrogen oxides (NO_x)
Carbon oxides (CO_x)

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· LD/LC50 values relevant for classification:		
2517-43-3 3-methoxybutan-1-ol		
Oral	LD50	3000 mg/kg (mouse)
100-51-6 benzyl alcohol		
Oral	LD50	1230 mg/kg (rat)
Dermal	LD50	2000 mg/kg (rabbit)
57-55-6 propylene glycol		
Oral	LD50	2000 mg/kg (rat)
Dermal	LD50	20800 mg/kg (rabbit)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Irritation may occur.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.

(Contd. on page 5)

EU

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 16.05.2019

Version number 3

Revision: 16.05.2019

Trade name: Stazon cleaner

(Contd. of page 4)

- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous to water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation** Disposal must be made according to official regulations.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

- | | |
|--|-----------------|
| · 14.1 UN-Number | Void |
| · 14.2 UN proper shipping name | Void |
| · 14.3 Transport hazard class(es) | Void |
| · 14.4 Packing group | Void |
| · 14.5 Environmental hazards: | |
| · Marine pollutant: | No |
| · 14.6 Special precautions for user | Not applicable. |
| · 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code | Not applicable. |

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

EU

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 16.05.2019

Version number 3

Revision: 16.05.2019

Trade name: Stazon cleaner

(Contd. of page 5)

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H226 Flammable liquid and vapour.
H302 Harmful if swallowed.
H312 Harmful in contact with skin.
H332 Harmful if inhaled.

· Department issuing SDS: Sales department**· Contact:** Phone number: +<81> 3-3834-1080 (Japan)**· Abbreviations and acronyms:**

GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
VOC: Volatile Organic Compounds (USA, EU)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Flam. Liq. 3: Flammable liquids – Category 3
Acute Tox. 4: Acute toxicity – Category 4

· * Data compared to the previous version altered.

Classification according to Regulation (EC) No 1272/2008

EU