

TECHNICAL DATA SHEET

Description: 2.4-2.5GHz SMA Stubby Antenna

PART NUMBER: W1095X



W1095

Features:

- · Fixed Stubby Low Profile Monopole Antenna
- · Gain 1 dBi
- Ingress Protection IP65
- UV Protection
- RoHS Compliant Product
- Connector Type: See page 2

Applications:

- WiFi, Zigbee, BLE/BT, WLAN (2.4-2.5GHz)
- Metering, Security, IoT **Applications**
- Mining, Utility, and Industrial **Applications**
- **Outdoor Networking**
- **Data Transmission**
- Access Points

W1095K W1095KRP

All dimensions are in mm / inches

Issue: 1843

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100

Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551

Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0

Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



TECHNICAL DATA SHEET

Description: 2.4-2.5GHz SMA Stubby Antenna

PART NUMBER: W1095X

Series: External Stubby

ELECTRICAL SPECIFICATIONS

Antenna Type	Monopole
Frequency	2400-2500MHz
Nominal Impedance	50 Ω
VSWR	2.5:1
Radiation Pattern	Omni
Gain	1dBi
Efficiency	50%
Polarization	Vertical

MECHANICAL SPECIFICATIONS

Overall Length 50.8mm Weight 4.1q Antenna Color / Material Black Connector type SMA Male (W1095)

> RA SMA Male (W1095K) RA RP SMA Male (W1095KRP)

> > Yes

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature -40°C~+85°C -40°C~+85°C Storage Temperature **IP** Rating **IP65**

Issue: 1843

RoHS Compliant





TECHNICAL DATA SHEET


Description: 2.4-2.5GHz SMA Stubby Antenna

PART NUMBER: W1095X


Series: External Stubby

MECHANICAL DRAWING

W1095



W1095K / W1095KRP








Description: 2.4-2.5GHz SMA Stubby Antenna

PART NUMBER: W1095X

TEST SETUP



Antenna is a monopole antenna. All data in this document is tested without any additional ground plane. Antenna in free space.








Description: 2.4-2.5GHz SMA Stubby Antenna

PART NUMBER: W1095X

CHARTS







Issue: 1843



TECHNICAL DATA SHEET

Description: 2.4-2.5G

Description: 2.4-2.5GHz SMA Stubby Antenna

PART NUMBER: W1095X


CHARTS

Free Space Radiation Pattern

Elevation Plane

x v


XZ Plane



Horizontal Plane



XY Plane





TECHNICAL DATA SHEET

Description: 2.4-2.5GHz SMA Stubby Antenna

PART NUMBER: W1095X

Series: External Stubby

PACKAGING

W1095

Pack 20pcs antenna in one PE bag, 100pcs PE bag (2000pcs Antenna) in one carton

W1095K / W1095KRP

Pack 20pcs antenna in one PE bag, 72pcs PE bag (1440pcs Antenna) in one carton

