

## Platinum Resistance Temperature Detector

M 222

Mseries PRTDs are designed for large volume applications where long term stability, interchangeability and accuracy over a large temperature range are vital. Typical applications are Automotive, White goods, HVAC, Energy management, Medical and Industrial equipment.

Nominal Resistance $R_0$	Tolerance	Order No. Plastic bag
100 Ohm at 0°C	DIN EN 60751, class B	32 208 548
	DIN EN 60751, class A	32 208 550
	DIN EN 60751, class 1/3 DIN	32 208 551
500 Ohm at 0°C	DIN EN 60751, class B	32 208 706
1000 Ohm at 0°C	DIN EN 60751, class B	32 208 571
	DIN EN 60751, class A	32 208 572
	DIN EN 60751, class 1/3 DIN	32 208 707

The measuring point for the nominal resistance is defined at 8 mm from the end of the sensor body.

### Specification

DIN EN 60751 (according to IEC 751)

### Temperature range

-70°C to +500°C (continuous operation)  
(temporary use to 550 °C possible)  
Tolerance class B: - 70 °C to + 500 °C  
Tolerance class A: - 50 °C to + 300 °C  
Tolerance class 1/3 DIN: 0 °C to + 150 °C

### Temperature coefficient

TCR = 3850 ppm/K

### Leads

Pt clad Ni wire  
Recommend connection technology:  
Welding, Crimping and Brazing

### Lead lengths (L)

10 mm +/- 1 mm

### Long-term stability

max.  $R_0$ -drift 0.04% after 1000 h at 500°C

### Vibration resistance

at least 40 g acceleration at 10 to 2000 Hz,  
depends on installation

### Shock resistance

at least 100 g acceleration with 8ms half sine  
wave, depends on installation

### Environmental conditions

unhoused for dry environments only

### Insulation resistance

> 100 M $\Omega$  at 20°C; > 2 M $\Omega$  at 500°C

### Self heating

0.4 K/mW at 0°C

### Response time


water current ( $v = 0.4$  m/s):  $t_{0.5} = 0.05$  s  
 $t_{0.9} = 0.15$  s  
air stream ( $v = 2$  m/s):  $t_{0.5} = 3.0$  s  
 $t_{0.9} = 10.0$  s

### Measuring current

100  $\Omega$ : 0.3 to 1.0 mA  
500  $\Omega$ : 0.1 to 0.7 mA  
1000  $\Omega$ : 0.1 bis 0.3 mA  
(self heating has to be considered)

### Note

Other tolerances, values of resistance and wire  
lengths are available on request.



We reserve the right to make alterations and technical data printed. All technical data serves as a guideline and does not guarantee particular properties to any products.

Heraeus Sensor Technology GmbH, Reinhard- Heraeus- Ring 23, 63801 Kleinostheim, Germany  
Phone: +49 (0) 6181/35-8098, Fax: +49 (0)6181/35-8101, E-Mail: [info.HSND@Heraeus.com](mailto:info.HSND@Heraeus.com) Web: [www.heraeus-sensor-technology.com](http://www.heraeus-sensor-technology.com)