# EAO – Your Expert Partner for **Human Machine Interfaces**

## 51-255.022D - Keylock switch 2 positions

#### 51-255.022D - Keylock switch 2 positions



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

 $\begin{array}{ll} \mbox{Mounting cut-out} & \mbox{$\varnothing$ 16 mm} \\ \mbox{Design} & \mbox{raised} \end{array}$ 

**Front** 

Front dimension 18 mm x 18 mm Front shape square

**Other Attributes** 

Weight 0,016 kg

Operating-/Indication part

Switching angle 90° right

**IP-Rating** 

Front protection IP65

**Connection Method** 

Terminal Solder 2.8 x 0.5 mm

**Actuator** 

Switching action Rest(a) - Maintain

Switching element

Rotary positions 2

Switching system Snap-action switching element

Switching current 5 A

Contacts 1 NC + 1 NO

Contact material

Switching voltage 250 V AC

**Function** 


Keylock switch

eao 🔳

# EAO – Your Expert Partner for **Human Machine Interfaces**


## 51-255.022D - Keylock switch 2 positions

#### **Dimensions**




H = Universal terminal 2.0 x 0.5 mm


#### **Mounting cut-outs**



### Wiring diagram



### **Switching positions**



### **Additional information**

Standard lock: DOM 311 Two keys are supplied with each key lock switch Optional lock numbers on request

#### Legend

Contacts: NC = Normally closed, NO = Normally open Switching action: A = Rest, C = Maintained