LM2574,LM2574HV

LM2574/LM2574HV SIMPLE SWITCHER 0.5A Step-Down Voltage Regulator



Literature Number: SNVS104B



LM2574/LM2574HV SIMPLE SWITCHER™ 0.5A Step-Down Voltage Regulator

General Description

The LM2574 series of regulators are monolithic integrated circuits that provide all the active functions for a step-down (buck) switching regulator, capable of driving a 0.5A load with excellent line and load regulation. These devices are available in fixed output voltages of 3.3V, 5V, 12V, 15V, and an adjustable output version.

Requiring a minimum number of external components, these regulators are simple to use and include internal frequency compensation and a fixed-frequency oscillator.

The LM2574 series offers a high-efficiency replacement for popular three-terminal linear regulators. Because of its high efficiency, the copper traces on the printed circuit board are normally the only heat sinking needed.

A standard series of inductors optimized for use with the LM2574 are available from several different manufacturers. This feature greatly simplifies the design of switch-mode power supplies.

Other features include a guaranteed $\pm 4\%$ tolerance on output voltage within specified input voltages and output load conditions, and $\pm 10\%$ on the oscillator frequency. External shutdown is included, featuring 50 μ A (typical) standby current. The output switch includes cycle-by-cycle current limiting, as well as thermal shutdown for full protection under fault conditions.


Features

- 3.3V, 5V, 12V, 15V, and adjustable output versions
- Adjustable version output voltage range, 1.23V to 37V (57V for HV version) ±4% max over line and load conditions
- Guaranteed 0.5A output current
- Wide input voltage range, 40V, up to 60V for HV version
- Requires only 4 external components
- 52 kHz fixed frequency internal oscillator
- TTL shutdown capability, low power standby mode
- High efficiency
- Uses readily available standard inductors
- Thermal shutdown and current limit protection

Applications

- Simple high-efficiency step-down (buck) regulator
- Efficient pre-regulator for linear regulators
- On-card switching regulators
- Positive to negative converter (Buck-Boost)

Typical Application (Fixed Output Voltage Versions)




Note: Pin numbers are for 8-pin DIP package.

Patent Pending

SIMPLE SWITCHER™ is a trademark of National Semiconductor Corporation

Connection Diagrams

8-Lead DIP




 $\ensuremath{^{\circ}}$ No internal connection, but should be soldered to PC board for best heat transfer.

Top View

Order Number LM2574-3.3HVN, LM2574HVN-5.0, LM2574HVN-12, LM2574HVN-15, LM2574HVN-ADJ, LM2574N-3.3, LM2574N-5.0, LM2574N-12, LM2574N-15 or LM2574N-ADJ See NS Package Number N08A

14-Lead Wide Surface Mount (WM)



Top View
Order Number LM2574HVM-3.3, LM2574HVM-5.0,
LM2574HVM-12, LM2574HVM-15, LM2574HVM-ADJ,
LM2574M-3.3 LM2574M-5.0, LM2574M-12,
LM2574M-15 or LM2574M-ADJ
See NS Package Number M14B

Absolute Maximum Ratings (Note 1)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/ Distributors for availability and specifications.

Maximum Supply Voltage

 $\begin{array}{c} LM2574 & 45V \\ LM2574HV & 63V \\ \hline ON /OFF Pin Input Voltage & -0.3V \leq V \leq +V_{IN} \end{array}$

Output Voltage to Ground

(Steady State) -1V

Minimum ESD Rating

(C = 100 pF, R = 1.5 kΩ) 2 kV

Storage Temperature Range -65°C to +150°C

Lead Temperature

 $\begin{array}{ccc} \mbox{(Soldering, 10 seconds)} & 260\mbox{°C} \\ \mbox{Maximum Junction Temperature} & 150\mbox{°C} \\ \mbox{Power Dissipation} & \mbox{Internally Limited} \end{array}$

Operating Ratings

Temperature Range

 $LM2574/LM2574HV -40^{\circ}C \le T_{J} \le +125^{\circ}C$

Supply Voltage

LM2574 40V LM2574HV 60V

LM2574-3.3, LM2574HV-3.3 Electrical Characteristics

Specifications with standard type face are for $T_J = 25^{\circ}C$, and those with **boldface type** apply over **full Operating Temperature Range**.

Symbol	Parameter	Conditions		M2574-3.3 2574HV-3.3	Units (Limits)
			Тур	Limit	
				(Note 2)	
SYSTEM	PARAMETERS (Note 3) Test Circuit Figure 2			
V _{OUT}	Output Voltage	V _{IN} = 12V, I _{LOAD} = 100 mA	3.3		V
				3.234	V(Min)
				3.366	V(Max)
V _{OUT}	Output Voltage	$4.75V \le V_{IN} \le 40V, \ 0.1A \le I_{LOAD} \le 0.5A$	3.3		V
	LM2574			3.168/ 3.135	V(Min)
				3.432/ 3.465	V(Max)
V _{OUT}	Output Voltage	$4.75V \le V_{IN} \le 60V, \ 0.1A \le I_{LOAD} \le 0.5A$	3.3		
	LM2574HV			3.168/ 3.135	V(Min)
				3.450/ 3.482	V(Max)
η	Efficiency	$V_{IN} = 12V, I_{LOAD} = 0.5A$	72		%

LM2574-5.0, LM2574HV-5.0 Electrical Characteristics

Specifications with standard type face are for $T_J = 25^{\circ}C$, and those with **boldface type** apply over **full Operating Temperature Range.**

Symbol	Parameter	Conditions	L	M2574-5.0	Units
			LM	12574HV-5.0	(Limits)
			Тур	Limit	
				(Note 2)	
SYSTEM	PARAMETERS (Note 3) Test Circuit <i>Figure 2</i>			
V _{OUT}	Output Voltage	V _{IN} = 12V, I _{LOAD} = 100 mA	5		V
				4.900	V(Min)
				5.100	V(Max)
V _{OUT}	Output Voltage	$7V \le V_{IN} \le 40V, \ 0.1A \le I_{LOAD} \le 0.5A$	5		V
	LM2574			4.800/ 4.750	V(Min)
				5.200/ 5.250	V(Max)
V _{OUT}	Output Voltage	$7V \le V_{IN} \le 60V, \ 0.1A \le I_{LOAD} \le 0.5A$	5		
	LM2574HV			4.800/ 4.750	V(Min)
				5.225/ 5.275	V(Max)

LM2574-5.0, LM2574HV-5.0 Electrical Characteristics (Continued)

Specifications with standard type face are for $T_J = 25$ °C, and those with **boldface type** apply over **full Operating Temperature Range**.

Symbol	Parameter	Conditions	LM2574-5.0 LM2574HV-5.0		Units (Limits)
			Тур	Limit	
				(Note 2)	
η	Efficiency	V _{IN} = 12V, I _{LOAD} = 0.5A	77		%

LM2574-12, LM2574HV-12 Electrical Characteristics

Specifications with standard type face are for $T_J = 25^{\circ}C$, and those with **boldface type** apply over **full Operating Temperature Range.**

Symbol	Parameter	Conditions		LM2574-12 LM2574HV-12	
			Тур	Limit	
				(Note 2)	
SYSTEM	PARAMETERS (Note 3) Test Circuit Figure 2			
V _{OUT}	Output Voltage	V _{IN} = 25V, I _{LOAD} = 100 mA	12		V
				11.76	V(Min)
				12.24	V(Max)
V _{OUT}	Output Voltage	$15V \le V_{IN} \le 40V, \ 0.1A \le I_{LOAD} \le 0.5A$	12		V
	LM2574			11.52/ 11.40	V(Min)
				12.48/ 12.60	V(Max)
V _{OUT}	Output Voltage	$15V \le V_{IN} \le 60V, \ 0.1A \le I_{LOAD} \le 0.5A$	12		
	LM2574HV			11.52/ 11.40	V(Min)
				12.54/ 12.66	V(Max)
η	Efficiency	V _{IN} = 15V, I _{LOAD} = 0.5A	88		%

LM2574-15, LM2574HV-15 Electrical Characteristics

Specifications with standard type face are for $T_J = 25^{\circ}C$, and those with **boldface type** apply over **full Operating Temperature Range.**

Symbol	Parameter	Conditions		LM2574-15 LM2574HV-15	
			Тур	Limit	(Limits)
				(Note 2)	
SYSTEM	PARAMETERS (Note 3	Test Circuit Figure 2			
V _{OUT}	Output Voltage	V _{IN} = 30V, I _{LOAD} = 100 mA	15		V
				14.70	V(Min)
				15.30	V(Max)
V _{OUT}	Output Voltage	$18V \le V_{IN} \le 40V, \ 0.1A \le I_{LOAD} \le 0.5A$	15		V
	LM2574			14.40/ 14.25	V(Min)
				15.60/ 15.75	V(Max)
V _{OUT}	Output Voltage	$18V \le V_{IN} \le 60V, \ 0.1A \le I_{LOAD} \le 0.5A$	15		
	LM2574HV			14.40/ 14.25	V(Min)
				15.68/ 15.83	V(Max)
η	Efficiency	V _{IN} = 18V, I _{LOAD} = 0.5A	88		%

LM2574-ADJ, LM2574HV-ADJ Electrical Characteristics

Specifications with standard type face are for $T_J = 25^{\circ}C$, and those with **boldface type** apply over **full Operating Temperature Range**. Unless otherwise specified, $V_{IN} = 12V$, $I_{LOAD} = 100$ mA.

Symbol	Parameter			LM2574-ADJ LM2574HV-ADJ	
			Тур	Limit	
				(Note 2)	
SYSTEM	PARAMETERS (Note 3) Test Circuit Figure 2			
V_{FB}	Feedback Voltage	$V_{IN} = 12V, I_{LOAD} = 100 \text{ mA}$	1.230		V
				1.217	V(Min)
				1.243	V(Max)
V _{FB}	Feedback Voltage	$7V \le V_{IN} \le 40V, \ 0.1A \le I_{LOAD} \le 0.5A$	1.230		V
	LM2574	V _{OUT} Programmed for 5V. Circuit of Figure 2		1.193/ 1.180	V(Min)
				1.267/ 1.280	V(Max)
V _{FB}	Feedback Voltage	$7V \le V_{IN} \le 60V, 0.1A \le I_{LOAD} \le 0.5A$	1.230		
	LM2574HV	V _{OUT} Programmed for 5V. Circuit of Figure 2		1.193/ 1.180	V(Min)
				1.273/ 1.286	V(Max)
η	Efficiency	$V_{IN} = 12V, V_{OUT} = 5V, I_{LOAD} = 0.5A$	77		%

All Output Voltage Versions Electrical Characteristics

Specifications with standard type face are for $T_J = 25\,^{\circ}\text{C}$, and those with **boldface type** apply over **full Operating Temperature Range.** Unless otherwise specified, $V_{IN} = 12V$ for the 3.3V, 5V, and Adjustable version, $V_{IN} = 25V$ for the 12V version, and $V_{IN} = 30V$ for the 15V version. $I_{LOAD} = 100$ mA.

Symbol	Parameter Conditions			12574-XX 2574HV-XX	Units (Limits)	
				Тур	Limit (Note 2)	
DEVICE P	PARAMETERS		-			-
l _b	Feedback Bias Adjustable Version Only, V _{OUT} = 5V Current		50	100/ 500	nA	
f _O	Oscillator Frequency	(see Note 10)	(see Note 10)		47/ 42 58/ 63	kHz kHz(Min) kHz(Max)
V _{SAT}	Saturation Voltage	I _{OUT} = 0.5A (Note 4)	I _{OUT} = 0.5A (Note 4)		1.2/ 1.4	V V(max)
DC	Max Duty Cycle (ON)	(Note 5)		98	93	% %(Min)
I _{CL}	Current Limit	Peak Current, (Notes 4, 10)		1.0	0.7/ 0.65 1.6/ 1.8	A A(Min) A(Max)
lL	Output Leakage Current	(Notes 6, 7)	(Notes 6, 7) Output = $0V$ Output = $-1V$ Output = $-1V$		2	mA(Max) mA mA(Max)
IQ	Quiescent Current	(Note 6)	·		10	mA mA(Max)
I _{STBY}	Standby Quiescent Current	ON /OFF Pin= 5V (OFF)		50	200	μA μA(Max)
θ_{JA} θ_{JA} θ_{JA}	Thermal Resistance	N Package, Junction to Am	N Package, Junction to Ambient (Note 8) N Package, Junction to Ambient (Note 9) M Package, Junction to Ambient (Note 8)			°C/W

All Output Voltage Versions Electrical Characteristics (Continued)

Specifications with standard type face are for $T_J = 25$ °C, and those with **boldface type** apply over **full Operating Tempera**ture Range. Unless otherwise specified, $V_{IN} = 12V$ for the 3.3V, 5V, and Adjustable version, $V_{IN} = 25V$ for the 12V version, and V_{IN} = 30V for the 15V version. I_{LOAD} = 100 mA.

Symbol	Parameter	Conditions		LM2574-XX LM2574HV-XX	
			Тур	Limit	7
				(Note 2)	
DEVICE P	PARAMETERS		•		•
θ_{JA}		M Package, Junction to Ambient (Note 9)	78		
ON /OFF	CONTROL Test Circuit	Figure 2			•
V _{IH}	ON /OFF Pin Logic	V _{OUT} = 0V	1.4	2.2/ 2.4	V(Min)
V _{IL}	Input Level	V _{OUT} = Nominal Output Voltage	1.2	1.0/ 0.8	V(Max)
I _H	ON /OFF Pin Input	ON /OFF Pin = 5V (OFF)	12		μA
	Current			30	μA(Max)
I _{IL}	1	ON /OFF Pin = 0V (ON)	0		μA
				10	μA(Max)

Note 1: Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but do not quarantee specific performance limits. For quaranteed specifications and test conditions, see the Electrical Characteristics.

Note 2: All limits guaranteed at room temperature (Standard type face) and at temperature extremes (bold type face). All room temperature limits are 100% production tested. All limits at temperature extremes are guaranteed via correlation using standard Statistical Quality Control (SQC) methods. All limits are used to calculate Average Outgoing Quality Level.

Note 3: External components such as the catch diode, inductor, input and output capacitors can affect switching regulator system performance. When the LM2574 is used as shown in the Figure 2 test circuit, system performance will be as shown in system parameters section of Electrical Characteristics.

- Note 4: Output pin sourcing current. No diode, inductor or capacitor connected to output pin.
- Note 5: Feedback pin removed from output and connected to 0V.
- Note 6: Feedback pin removed from output and connected to +12V for the Adjustable, 3.3V, and 5V versions, and +25V for the 12V and 15V versions, to force the output transistor OFF.
- Note 7: V_{IN} = 40V (60V for high voltage version).
- Note 8: Junction to ambient thermal resistance with approximately 1 square inch of printed circuit board copper surrounding the leads. Additional copper area will lower thermal resistance further. See application hints in this data sheet and the thermal model in Switchers Made Simple software.


Note 9: Junction to ambient thermal resistance with approximately 4 square inches of 1 oz. (0.0014 in. thick) printed circuit board copper surrounding the leads. Additional copper area will lower thermal resistance further. (See Note 8.)

Note 10: The oscillator frequency reduces to approximately 18 kHz in the event of an output short or an overload which causes the regulated output voltage to drop approximately 40% from the nominal output voltage. This self protection feature lowers the average power dissipation of the IC by lowering the minimum duty cycle from 5% down to approximately 2%.

Typical Performance Characteristics


Normalized Output Voltage

(Circuit of Figure 2)





JUNCTION TEMPERATURE (°C) 01139427






Typical Performance Characteristics (Circuit of Figure 2) (Continued)












Standby Quiescent Current




Oscillator Frequency




Switch Saturation Voltage




Typical Performance Characteristics (Circuit of Figure 2) (Continued)









Feedback Pin Current




Minimum Operating Voltage



Feedback Voltage vs Duty Cycle




Junction to Ambient Thermal Resistance



Typical Performance Characteristics (Circuit of Figure 2) (Continued)

Continuous Mode Switching Waveforms V_{OUT} = 5V, 500 mA Load Current, L = 330 μ H



Notes:

A: Output Pin Voltage, 10V/div


B: Inductor Current, 0.2 A/div

C: Output Ripple Voltage, 20 mV/div,

AC-Coupled

Horizontal Time Base: 5 µs/div

500 mA Load Transient Response for Continuous Mode Operation. L = 330 μ H, C_{OUT} = 300 μ F



01139408

01139406


Notes:

A: Output Voltage, 50 mV/div.

AC Coupled

B: 100 mA to 500 mA Load Pulse Horizontal Time Base: 200 μ s/div

Discontinuous Mode Switching Waveforms $V_{OUT} = 5V$, 100 mA Load Current, L = 100 μ H



01139407

Notes:

A: Output Pin Voltage, 10V/div


B: Inductor Current, 0.2 A/div

C: Output Ripple Voltage, 20 mV/div,

AC-Coupled

Horizontal Time Base: 5 µs/div

250 mA Load Transient Response for Discontinuous Mode Operation. L = 68 μH, C_{OUT} = 470 μF



01139409


Notes:

A: Output Voltage, 50 mV/div.

AC Coupled

B: 50 mA to 250 mA Load Pulse Horizontal Time Base: 200 µs/div

Block Diagram



R1 = 1K3.3V, R2 = 1.7k

5V, R2 = 3.1k

12V, R2 = 8.84k

15V, R2 = 11.3k

For Adj. Version


 $\text{R1 = Open, R2 = } 0\Omega$

Note: Pin numbers are for the 8-pin DIP package.

FIGURE 1.

Test Circuit and Layout Guidelines

Fixed Output Voltage Versions



 C_{IN} — 22 $\mu\text{F},\,75\text{V}$

Aluminum Electrolytic

 $C_{\mbox{\scriptsize OUT}}$ — 220 $\mu\mbox{\scriptsize F},\,25\mbox{\scriptsize V}$

Aluminum Electrolytic

D1 — Schottky, 11DQ06

L1 — 330 µH, 52627


(for 5V in, 3.3V out, use

100 μH, RL-1284-100)

R1 — 2k, 0.1%

R2 — 6.12k, 0.1%

Adjustable Output Voltage Version



$$V_{OUT} = V_{REF} \left(1 + \frac{R_2}{R_1} \right)$$

$$R_2 = R_1 \left(\frac{v_{OUT}}{v_{REF}} - 1 \right)$$

where $V_{REF} = 1.23V$,

R1 between 1k & 5k.

FIGURE 2.

As in any switching regulator, layout is very important. Rapidly switching currents associated with wiring inductance generate voltage transients which can cause problems. For minimal inductance and ground loops, the length of the leads indicated by heavy lines should be kept as short as

possible. Single-point grounding (as indicated) or ground plane construction should be used for best results. When using the Adjustable version, physically locate the programming resistors near the regulator, to keep the sensitive feedback wiring short.

Test Circuit and Layout Guidelines

(Continued)

Inductor	Pulse Eng.	Renco	NPI
Value	(Note 1)	(Note 2)	(Note 3)
68 µH	*	RL-1284-68-43	NP5915
100 µH	*	RL-1284-100-43	NP5916
150 µH	52625	RL-1284-150-43	NP5917
220 µH	52626	RL-1284-220-43	NP5918/5919
330 µH	52627	RL-1284-330-43	NP5920/5921
470 µH	52628	RL-1284-470-43	NP5922
680 µH	52629	RL-1283-680-43	NP5923
1000 µH	52631	RL-1283-1000-43	*
1500 µH	*	RL-1283-1500-43	*
2200 µH	*	RL-1283-2200-43	*

FIGURE 3. Inductor Selection by Manufacturer's Part Number

U.S. Source

Note 1: Pulse Engineering, (619) 674-8100

P.O. Box 12236, San Diego, CA 92112

Note 2: Renco Electronics Inc., (516) 586-5566 60 Jeffryn Blvd. East, Deer Park, NY 11729

*Contact Manufacturer

*Contact Manufacturer

European Source Note 3: NPI/APC +44 (0) 634 290588 47 Riverside, Medway City Estate Strood, Rochester, Kent ME2 4DP. UK

LM2574 Series Buck Regulator Design Procedure

PROCEDURE (Fixed Output Voltage Versions)

Given: V_{OUT} = Regulated Output Voltage (3.3V, 5V, 12V, or 15V) $V_{IN}(Max)$ = Maximum Input Voltage $I_{LOAD}(Max)$ = Maximum Load Current

1. Inductor Selection (L1)

- **A.** Select the correct Inductor value selection guide from *Figures 4, 5, 6*, or *Figure 7.* (Output voltages of 3.3V, 5V, 12V or 15V respectively). For other output voltages, see the design procedure for the adjustable version.
- **B.** From the inductor value selection guide, identify the inductance region intersected by $V_{IN}(\text{Max})$ and $I_{\text{LOAD}}(\text{Max})$.
- **C.** Select an appropriate inductor from the table shown in *Figure 3*. Part numbers are listed for three inductor manufacturers. The inductor chosen must be rated for operation at the LM2574 switching frequency (52 kHz) and for a current rating of 1.5 x I_{LOAD} . For additional inductor information, see the inductor section in the Application Hints section of this data sheet.

2. Output Capacitor Selection (Cout)

- **A.** The value of the output capacitor together with the inductor defines the dominate pole-pair of the switching regulator loop. For stable operation and an acceptable output ripple voltage, (approximately 1% of the output voltage) a value between 100 μ F and 470 μ F is recommended.
- **B.** The capacitor's voltage rating should be at least 1.5 times greater than the output voltage. For a 5V regulator, a rating of at least 8V is appropriate, and a 10V or 15V rating is recommended.

Higher voltage electrolytic capacitors generally have lower ESR numbers, and for this reason it may be necessary to select a capacitor rated for a higher voltage than would normally be needed.

3. Catch Diode Selection (D1)

- **A.** The catch-diode current rating must be at least 1.5 times greater than the maximum load current. Also, if the power supply design must withstand a continuous output short, the diode should have a current rating equal to the maximum current limit of the LM2574. The most stressful condition for this diode is an overload or shorted output condition.
- **B.** The reverse voltage rating of the diode should be at least 1.25 times the maximum input voltage.

4. Input Capacitor (C_{IN})

An aluminum or tantalum electrolytic bypass capacitor located close to the regulator is needed for stable operation.

EXAMPLE (Fixed Output Voltage Versions)

Given: $V_{OUT} = 5V V_{IN}(Max) = 15V I_{LOAD}(Max) = 0.4A$

1. Inductor Selection (L1)

- A. Use the selection guide shown in Figure 5.
- **B.** From the selection guide, the inductance area intersected by the 15V line and 0.4A line is 330.
- **C.** Inductor value required is 330 μ H. From the table in *Figure 3*, choose Pulse Engineering PE-52627, Renco RL-1284-330, or NPI NP5920/5921.

2. Output Capacitor Selection (C_{OUT})

- **A.** C_{OUT} = 100 μF to 470 μF standard aluminum electrolytic.
- **B.** Capacitor voltage rating = 20V.

3. Catch Diode Selection (D1)

- A. For this example, a 1A current rating is adequate.
- **B.** Use a 20V 1N5817 or SR102 Schottky diode, or any of the suggested fast-recovery diodes shown in *Figure 9*.

4. Input Capacitor (CIN)

A 22 μF aluminum electrolytic capacitor located near the input and ground pins provides sufficient bypassing.

INDUCTOR VALUE SELECTION GUIDES (For Continuous Mode Operation)




FIGURE 4. LM2574HV-3.3 Inductor Selection Guide




FIGURE 5. LM2574HV-5.0 Inductor Selection Guide




FIGURE 6. LM2574HV-12 Inductor Selection Guide




FIGURE 7. LM2574HV-15 Inductor Selection Guide




FIGURE 8. LM2574HV-ADJ Inductor Selection Guide

PROCEDURE (Adjustable Output Voltage Versions)

Given: V_{OUT} = Regulated Output Voltage V_{IN}(Max) = Maximum Input Voltage I_{LOAD}(Max) = Maximum Load Current F = Switching Frequency (Fixed at 52 kHz)

1. Programming Output Voltage (Selecting R1 and R2, as shown in Figure 2) Use the following formula to select the appropriate resistor values.

$$V_{OUT} = V_{REF} \left(1 + \frac{R_2}{R_1} \right)$$
 where $V_{REF} = 1.23V$

R₁ can be between 1k and 5k. (For best temperature coefficient and stability with time, use 1% metal film resistors)

$$R_2 = R_1 \left(\frac{V_{OUT}}{V_{REF}} - 1 \right)$$

2. Inductor Selection (L1)

A. Calculate the inductor Volt • microsecond constant, E • T (V • μs), from the following formula:

$$E \bullet T = (V_{IN} - V_{OUT}) \frac{V_{OUT}}{V_{IN}} \bullet \frac{1000}{F (in kHz)} (V \bullet \mu s)$$

 $E \bullet T = (V_{IN} - V_{OUT}) \frac{V_{OUT}}{V_{IN}} \bullet \frac{1000}{F \textit{(in kHz)}} (V \bullet \mu s)$ **B.** Use the E • T value from the previous formula and match it with the E • T number on the vertical axis of the **Inductor** Value Selection Guide shown in Figure 8.

C. On the horizontal axis, select the maximum load current. D. Identify the inductance region intersected by the E • T value and the maximum load current value, and note the inductor value for that region.

E. Select an appropriate inductor from the table shown in Figure 3. Part numbers are listed for three inductor manufacturers. The inductor chosen must be rated for operation at the LM2574 switching frequency (52 kHz) and for a current rating of 1.5 x $I_{\rm LOAD}$. For additional inductor information, see the inductor section in the application hints section of this data sheet

EXAMPLE (Adjustable Output Voltage Versions)

Given: $V_{OUT} = 24V V_{IN}(Max) = 40V I_{LOAD}(Max) = 0.4A F =$ 52 kHz

1. Programming Output Voltage (Selecting R1 and R2)

$$V_{OUT} = 1.23 \left(1 + \frac{R_2}{R_1} \right) \qquad \text{Select R1} = 1 \text{k}$$

$$R_2 = R_1 \left(\frac{V_{OUT}}{V_{REF}} - 1 \right) = 1 \text{k} \left(\frac{24V}{1.23V} - 1 \right)$$

$$R_2 = 1 \text{k} (19.51 - 1) = 18.51 \text{k, closest } 1\% \text{ value is } 18.7 \text{k}$$

2. Inductor Selection (L1)

A. Calculate E • T (V • μs)

$$E \bullet T = (40 - 24) \bullet \frac{24}{40} \bullet \frac{1000}{52} = 185 \text{ V} \bullet \mu\text{s}$$

B. E • T = 185 V • μs C. $I_{LOAD}(Max) = 0.4A$

D. Inductance Region = 1000

E. Inductor Value = 1000 μH Choose from**Pulse Engineering** Part #PE-52631, or Renco Part #RL-1283-1000.

PROCEDURE (Adjustable Output Voltage Versions)

3. Output Capacitor Selection (COUT)

A. The value of the output capacitor together with the inductor defines the dominate pole-pair of the switching regulator loop. For stable operation, the capacitor must satisfy the following requirement:

$$C_{OUT} \ge 13,300 \frac{V_{IN}(Max)}{V_{OUT} \bullet L(\mu H)} (\mu F)$$

The above formula yields capacitor values between 5 μ F and 1000 μ F that will satisfy the loop requirements for stable operation. But to achieve an acceptable output ripple voltage, (approximately 1% of the output voltage) and transient response, the output capacitor may need to be several times larger than the above formula yields.

B. The capacitor's voltage rating should be at last 1.5 times greater than the output voltage. For a 24V regulator, a rating of at least 35V is recommended. Higher voltage electrolytic capacitors generally have lower ESR numbers, and for this reasion it may be necessary to select a capacitor rate for a higher voltage than would normally be needed.

4. Catch Diode Selection (D1)

- **A.** The catch-diode current rating must be at least 1.5 times greater than the maximum load current. Also, if the power supply design must withstand a continuous output short, the diode should have a current rating equal to the maximum current limit of the LM2574. The most stressful condition for this diode is an overload or shorted output condition. Suitable diodes are shown in the selection guide of *Figure 9*.
- **B.** The reverse voltage rating of the diode should be at least 1.25 times the maximum input voltage.
- 5. Input Capacitor (C_{IN}) An aluminum or tantalum electrolytic bypass capacitor located close to the regulator is needed for stable operation.

EXAMPLE (Adjustable Output Voltage Versions)

3. Output Capacitor Selection (Cout)

A.
$$C_{OUT} > 13,300 \frac{40}{24 \cdot 1000} = 22.2 \ \mu F$$

However, for acceptable output ripple voltage select $C_{OUT} \ge 100~\mu F$ $C_{OUT} = 100~\mu F$ electrolytic capacitor

4. Catch Diode Selection (D1)

- A. For this example, a 1A current rating is adequate.
- **B.** Use a 50V MBR150 or 11DQ05 Schottky diode, or any of the suggested fast-recovery diodes in *Figure 9*.

5. Input Capacitor (C_{IN})

A 22 μ F aluminum electrolytic capacitor located near the input and ground pins provides sufficient bypassing. See (*Figure 9*).

To further simplify the buck regulator design procedure, National Semiconductor is making available computer design software to be used with the Simple Switcher line of switching regulators. **Switchers Made Simple** (version 3.3) is available on a (31/2) diskette for IBM compatible computers from a National Semiconductor sales office in your area.

V _R	1 A	mp Diodes
	Schottky	Fast Recovery
20V	1N5817	
	SR102	
	MBR120P	
30V	1N5818	
	SR103	
	11DQ03	The
	MBR130P	following
	10JQ030	diodes
40V	1N5819	are all
	SR104	rated to
	11DQ04	100V
	11JQ04	
	MBR140P	
50V	MBR150	11DF1
	SR105	10JF1
	11DQ05	MUR110
	11JQ05	HER102
60V	MBR160	
	SR106	
	11DQ06	
	11JQ06	
90V	11DQ09	

FIGURE 9. Diode Selection Guide

Application Hints

INPUT CAPACITOR (CIN)

To maintain stability, the regulator input pin must be by-passed with at least a 22 μF electrolytic capacitor. The capacitor's leads must be kept short, and located near the regulator.

If the operating temperature range includes temperatures below -25°C, the input capacitor value may need to be larger. With most electrolytic capacitors, the capacitance value decreases and the ESR increases with lower temperatures and age. Paralleling a ceramic or solid tantalum capacitor will increase the regulator stability at cold temperatures. For maximum capacitor operating lifetime, the capacitor's RMS ripple current rating should be greater than

$$\begin{split} &1.2 \times \left(\frac{t_{ON}}{T}\right) \times I_{LOAD} \\ &\text{where } \frac{t_{ON}}{T} = \frac{V_{OUT}}{V_{IN}} \text{ for a buck regulator} \\ &\text{and } \frac{t_{ON}}{T} = \frac{|V_{OUT}|}{|V_{OUT}| + V_{IN}} \text{ for a buck-boost regulator.} \end{split}$$

INDUCTOR SELECTION

All switching regulators have two basic modes of operation: continuous and discontinuous. The difference between the two types relates to the inductor current, whether it is flowing continuously, or if it drops to zero for a period of time in the normal switching cycle. Each mode has distinctively different operating characteristics, which can affect the regulator performance and requirements.

The LM2574 (or any of the Simple Switcher family) can be used for both continuous and discontinuous modes of operation.

In many cases the preferred mode of operation is in the continuous mode. It offers better load regulation, lower peak switch, inductor and diode currents, and can have lower output ripple voltage. But it does require relatively large inductor values to keep the inductor current flowing continuously, especially at low output load currents.

To simplify the inductor selection process, an inductor selection guide (nomograph) was designed (see *Figure 4* through *Figure 8*). This guide assumes continuous mode operation, and selects an inductor that will allow a peak-to-peak inductor ripple current (ΔI_{IND}) to be a certain percentage of the maximum design load current. In the LM2574 SIMPLE SWITCHER, the peak-to-peak inductor ripple current percentage (of load current) is allowed to change as different design load currents are selected. By allowing the percentage of inductor ripple current to increase for lower current applications, the inductor size and value can be kept relatively low.

Application Hints (Continued)

INDUCTOR RIPPLE CURRENT

When the switcher is operating in the continuous mode, the inductor current waveform ranges from a triangular to a sawtooth type of waveform (depending on the input voltage). For a given input voltage and output voltage, the peak-to-peak amplitude of this inductor current waveform remains constant. As the load current rises or falls, the entire saw-tooth current waveform also rises or falls. The average DC value of this waveform is equal to the DC load current (in the buck regulator configuration).

If the load current drops to a low enough level, the bottom of the sawtooth current waveform will reach zero, and the switcher will change to a discontinuous mode of operation. This is a perfectly acceptable mode of operation. Any buck switching regulator (no matter how large the inductor value is) will be forced to run discontinuous if the load current is light enough.

The curve shown in *Figure 10* illustrates how the peak-to-peak inductor ripple current ($\Delta I_{\rm IND}$) is allowed to change as different maximum load currents are selected, and also how it changes as the operating point varies from the upper border to the lower border within an inductance region (see Inductor Selection guides).




FIGURE 10. Inductor Ripple Current (ΔI_{IND}) Range Based on Selection Guides from *Figure 4* through *Figure 8*.

Consider the following example:

 $V_{OUT} = 5V @ 0.4A$

 $V_{IN} = 10V$ minimum up to 20V maximum

The selection guide in *Figure 5* shows that for a 0.4A load current, and an input voltage range between 10V and 20V, the inductance region selected by the guide is 330 μH . This value of inductance will allow a peak-to-peak inductor ripple current $(\Delta I_{\rm IND})$ to flow that will be a percentage of the maximum load current. For this inductor value, the $\Delta I_{\rm IND}$ will also vary depending on the input voltage. As the input voltage increases to 20V, it approaches the upper border of the inductance region, and the inductor ripple current increases. Referring to the curve in *Figure 10*, it can be seen that at the 0.4A load current level, and operating near the upper border of the 330 μH inductance region, the $\Delta I_{\rm IND}$ will be 53% of 0.4A, or 212 mA p-p.

This ΔI_{IND} is important because from this number the peak inductor current rating can be determined, the minimum load

current required before the circuit goes to discontinuous operation, and also, knowing the ESR of the output capacitor, the output ripple voltage can be calculated, or conversely, measuring the output ripple voltage and knowing the ΔI_{IND} , the ESR can be calculated.

From the previous example, the Peak-to-peak Inductor Ripple Current (ΔI_{IND}) = 212 mA p-p. Once the Δ_{IND} value is known, the following three formulas can be used to calculate additional information about the switching regulator circuit:

1. Peak Inductor or peak switch current

$$= \left(I_{\text{LOAD}} + \frac{\Delta I_{\text{IND}}}{2}\right) = \left(0.4A + \frac{212}{2}\right) = 506 \text{ mA}$$

Minimum load current before the circuit becomes discontinuous

$$=\frac{\Delta I_{IND}}{2}=\frac{212}{2}=106 \text{ mA}$$

3. Output Ripple Voltage = (ΔI_{IND}) x (ESR of C_{OUT})

The selection guide chooses inductor values suitable for continuous mode operation, but if the inductor value chosen is prohibitively high, the designer should investigate the possibility of discontinuous operation. The computer design software *Switchers Made Simple* will provide all component values for discontinuous (as well as continuous) mode of operation.

Inductors are available in different styles such as pot core, toroid, E-frame, bobbin core, etc., as well as different core materials, such as ferrites and powdered iron. The least expensive, the bobbin core type, consists of wire wrapped on a ferrite rod core. This type of construction makes for an inexpensive inductor, but since the magnetic flux is not completely contained within the core, it generates more electromagnetic interference (EMI). This EMI can cause problems in sensitive circuits, or can give incorrect scope readings because of induced voltages in the scope probe.

The inductors listed in the selection chart include powdered iron toroid for Pulse Engineering, and ferrite bobbin core for Benco.

An inductor should not be operated beyond its maximum rated current because it may saturate. When an inductor begins to saturate, the inductance decreases rapidly and the inductor begins to look mainly resistive (the DC resistance of the winding). This can cause the inductor current to rise very rapidly and will affect the energy storage capabilities of the inductor and could cause inductor overheating. Different inductor types have different saturation characteristics, and this should be kept in mind when selecting an inductor. The inductor manufacturers' data sheets include current and energy limits to avoid inductor saturation.

OUTPUT CAPACITOR

An output capacitor is required to filter the output voltage and is needed for loop stability. The capacitor should be located near the LM2574 using short pc board traces. Standard aluminum electrolytics are usually adequate, but low ESR types are recommended for low output ripple voltage and good stability. The ESR of a capacitor depends on many factors, some which are: the value, the voltage rating, physical size and the type of construction. In general, low value or low voltage (less than 12V) electrolytic capacitors usually have higher ESR numbers.

Application Hints (Continued)

The amount of output ripple voltage is primarily a function of the ESR (Equivalent Series Resistance) of the output capacitor and the amplitude of the inductor ripple current (ΔI_{IND}). See the section on inductor ripple current in Application Hints.

The lower capacitor values (100 μ F- 330 μ F) will allow typically 50 mV to 150 mV of output ripple voltage, while larger-value capacitors will reduce the ripple to approximately 20 mV to 50 mV.

Output Ripple Voltage = (ΔI_{IND}) (ESR of C_{OUT})

To further reduce the output ripple voltage, several standard electrolytic capacitors may be paralleled, or a higher-grade capacitor may be used. Such capacitors are often called "high-frequency," "low-inductance," or "low-ESR." These will reduce the output ripple to 10 mV or 20 mV. However, when operating in the continuous mode, reducing the ESR below 0.03Ω can cause instability in the regulator.

Tantalum capacitors can have a very low ESR, and should be carefully evaluated if it is the only output capacitor. Because of their good low temperature characteristics, a tantalum can be used in parallel with aluminum electrolytics, with the tantalum making up 10% or 20% of the total capacitance.

The capacitor's ripple current rating at 52 kHz should be at least 50% higher than the peak-to-peak inductor ripple current.

CATCH DIODE

Buck regulators require a diode to provide a return path for the inductor current when the switch is off. This diode should be located close to the LM2574 using short leads and short printed circuit traces.

Because of their fast switching speed and low forward voltage drop, Schottky diodes provide the best efficiency, especially in low output voltage switching regulators (less than 5V). Fast-Recovery, High-Efficiency, or Ultra-Fast Recovery diodes are also suitable, but some types with an abrupt turn-off characteristic may cause instability and EMI problems. A fast-recovery diode with soft recovery characteristics is a better choice. Standard 60 Hz diodes (e.g., 1N4001 or 1N5400, etc.) are also **not suitable.** See *Figure 9* for Schottky and "soft" fast-recovery diode selection guide.

OUTPUT VOLTAGE RIPPLE AND TRANSIENTS

The output voltage of a switching power supply will contain a sawtooth ripple voltage at the switcher frequency, typically about 1% of the output voltage, and may also contain short voltage spikes at the peaks of the sawtooth waveform.

The output ripple voltage is due mainly to the inductor sawtooth ripple current multiplied by the ESR of the output capacitor. (See the inductor selection in the application hints.)

The voltage spikes are present because of the the fast switching action of the output switch, and the parasitic inductance of the output filter capacitor. To minimize these voltage spikes, special low inductance capacitors can be used, and their lead lengths must be kept short. Wiring inductance, stray capacitance, as well as the scope probe used to evaluate these transients, all contribute to the amplitude of these spikes.

An additional small LC filter (20 μ H & 100 μ F) can be added to the output (as shown in *Figure 16*) to further reduce the

amount of output ripple and transients. A 10 x reduction in output ripple voltage and transients is possible with this filter.

FEEDBACK CONNECTION

The LM2574 (fixed voltage versions) feedback pin must be wired to the output voltage point of the switching power supply. When using the adjustable version, physically locate both output voltage programming resistors near the LM2574 to avoid picking up unwanted noise. Avoid using resistors greater than 100 k Ω because of the increased chance of noise pickup.

ON /OFF INPUT

For normal operation, the $\overline{\text{ON}}$ /OFF pin should be grounded or driven with a low-level TTL voltage (typically below 1.6V). To put the regulator into standby mode, drive this pin with a high-level TTL or CMOS signal. The $\overline{\text{ON}}$ /OFF pin can be safely pulled up to +V_{IN} without a resistor in series with it. The $\overline{\text{ON}}$ /OFF pin should not be left open.

GROUNDING

The 8-pin molded DIP and the 14-pin surface mount package have separate power and signal ground pins. Both ground pins should be soldered directly to wide printed circuit board copper traces to assure low inductance connections and good thermal properties.

THERMAL CONSIDERATIONS

The 8-pin DIP (N) package and the 14-pin Surface Mount (M) package are molded plastic packages with solid copper lead frames. The copper lead frame conducts the majority of the heat from the die, through the leads, to the printed circuit board copper, which acts as the heat sink. For best thermal performance, wide copper traces should be used, and all ground and unused pins should be soldered to generous amounts of printed circuit board copper, such as a ground plane. Large areas of copper provide the best transfer of heat (lower thermal resistance) to the surrounding air, and even double-sided or multilayer boards provide better heat paths to the surrounding air. Unless the power levels are small, using a socket for the 8-pin package is not recommended because of the additional thermal resistance it introduces, and the resultant higher junction temperature.

Because of the 0.5A current rating of the LM2574, the total package power dissipation for this switcher is quite low, ranging from approximately 0.1W up to 0.75W under varying conditions. In a carefully engineered printed circuit board, both the N and the M package can easily dissipate up to 0.75W, even at ambient temperatures of 60°C, and still keep the maximum junction temperature below 125°C.

A curve displaying thermal resistance vs. pc board area for the two packages is shown in the Typical Performance Characteristics curves section of this data sheet.

These thermal resistance numbers are approximate, and there can be many factors that will affect the final thermal resistance. Some of these factors include board size, shape, thickness, position, location, and board temperature. Other factors are, the area of printed circuit copper, copper thickness, trace width, multi-layer, single- or double-sided, and the amount of solder on the board. The effectiveness of the pc board to dissipate heat also depends on the size, number and spacing of other components on the board. Furthermore, some of these components, such as the catch diode and inductor will generate some additional heat. Also, the thermal resistance decreases as the power level increases

Application Hints (Continued)

because of the increased air current activity at the higher power levels, and the lower surface to air resistance coefficient at higher temperatures.

The data sheet thermal resistance curves and the thermal model in *Switchers Made Simple* software (version 3.3) can estimate the maximum junction temperature based on operating conditions. In addition, the junction temperature can be estimated in actual circuit operation by using the following equation.

$$T_i = T_{cu} + (\theta_{i-cu} \times P_D)$$

With the switcher operating under worst case conditions and all other components on the board in the intended enclosure, measure the copper temperature ($T_{\rm cu}$) near the IC. This can be done by temporarily soldering a small thermocouple to the pc board copper near the IC, or by holding a small thermocouple on the pc board copper using thermal grease for good thermal conduction.

The thermal resistance $(\theta_{j\text{-cu}})$ for the two packages is: $\theta_{j\text{-cu}}$ = 42°C/W for the N-8 package

$$\theta_{j-cu} = 52^{\circ}C/W$$
 for the M-14 package

The power dissipation $(P_{\rm D})$ for the IC could be measured, or it can be estimated by using the formula:


$$P_D = (V_{IN}) (I_S) + \left(\frac{V_O}{V_{IN}}\right) (I_{LOAD}) (V_{SAT})$$

Where I_S is obtained from the typical supply current curve (adjustable version use the supply current vs. duty cycle curve).

Additional Applications

INVERTING REGULATOR

Figure 11 shows a LM2574-12 in a buck-boost configuration to generate a negative 12V output from a positive input voltage. This circuit bootstraps the regulator's ground pin to the negative output voltage, then by grounding the feedback pin, the regulator senses the inverted output voltage and regulates it to –12V.



Note: Pin numbers are for the 8-pin DIP package

FIGURE 11. Inverting Buck-Boost Develops -12V

For an input voltage of 8V or more, the maximum available output current in this configuration is approximately 100 mA. At lighter loads, the minimum input voltage required drops to approximately 4.7V.

The switch currents in this buck-boost configuration are higher than in the standard buck-mode design, thus lowering the available output current. Also, the start-up input current of the buck-boost converter is higher than the standard buck-mode regulator, and this may overload an input power source with a current limit less than 0.6A. Using a delayed turn-on or an undervoltage lockout circuit (described in the next section) would allow the input voltage to rise to a high enough level before the switcher would be allowed to turn on

Because of the structural differences between the buck and the buck-boost regulator topologies, the buck regulator design procedure section can not be used to to select the inductor or the output capacitor. The recommended range of inductor values for the buck-boost design is between 68 μH and 220 μH , and the output capacitor values must be larger than what is normally required for buck designs. Low input voltages or high output currents require a large value output capacitor (in the thousands of micro Farads).

The peak inductor current, which is the same as the peak switch current, can be calculated from the following formula:

$$I_{p} \approx \frac{I_{LOAD}\left(V_{IN} + |V_{O}|\right)}{V_{IN}} + \frac{V_{IN}\left|V_{O}\right|}{V_{IN} + |V_{O}|} \times \frac{1}{2L_{1} \: f_{osc}}$$

Where $f_{\rm osc}=52$ kHz. Under normal continuous inductor current operating conditions, the minimum $V_{\rm IN}$ represents the worst case. Select an inductor that is rated for the peak current anticipated.


Also, the maximum voltage appearing across the regulator is the absolute sum of the input and output voltage. For a –12V output, the maximum input voltage for the LM2574 is +28V, or +48V for the LM2574HV.

The *Switchers Made Simple* version 3.3) design software can be used to determine the feasibility of regulator designs using different topologies, different input-output parameters, different components, etc.

NEGATIVE BOOST REGULATOR

Another variation on the buck-boost topology is the negative boost configuration. The circuit in *Figure 12* accepts an input voltage ranging from –5V to –12V and provides a regulated –12V output. Input voltages greater than –12V will cause the output to rise above –12V, but will not damage the regulator.

Additional Applications (Continued)



Note: Pin numbers are for 8-pin DIP package.


FIGURE 12. Negative Boost

Because of the boosting function of this type of regulator, the switch current is relatively high, especially at low input voltages. Output load current limitations are a result of the maximum current rating of the switch. Also, boost regulators can not provide current limiting load protection in the event of a shorted load, so some other means (such as a fuse) may be necessary.

UNDERVOLTAGE LOCKOUT

In some applications it is desirable to keep the regulator off until the input voltage reaches a certain threshold. An undervoltage lockout circuit which accomplishes this task is shown in *Figure 13* while *Figure 14* shows the same circuit applied to a buck-boost configuration. These circuits keep the regulator off until the input voltage reaches a predetermined level.


$$V_{TH} \approx V_{Z1} + 2V_{BE} (Q1)$$



Note: Complete circuit not shown.

Note: Pin numbers are for 8-pin DIP package.

FIGURE 13. Undervoltage Lockout for Buck Circuit



Note: Complete circuit not shown (see Figure 11).

Note: Pin numbers are for 8-pin DIP package.


FIGURE 14. Undervoltage Lockout for Buck-Boost Circuit

DELAYED STARTUP

The $\overline{\text{ON}}$ /OFF pin can be used to provide a delayed startup feature as shown in *Figure 15*. With an input voltage of 20V and for the part values shown, the circuit provides approximately 10 ms of delay time before the circuit begins switching. Increasing the RC time constant can provide longer delay times. But excessively large RC time constants can cause problems with input voltages that are high in 60 Hz or 120 Hz ripple, by coupling the ripple into the $\overline{\text{ON}}$ /OFF pin.

ADJUSTABLE OUTPUT, LOW-RIPPLE POWER SUPPLY

A 500 mA power supply that features an adjustable output voltage is shown in *Figure 16*. An additional L-C filter that reduces the output ripple by a factor of 10 or more is included in this circuit.




Note: Complete circuit not shown.

Note: Pin numbers are for 8-pin DIP package.

FIGURE 15. Delayed Startup

Additional Applications (Continued)



Note: Pin numbers are for 8-pin DIP package.

FIGURE 16. 1.2V to 55V Adjustable 500 mA Power Supply with Low Output Ripple

Definition of Terms

BUCK REGULATOR

A switching regulator topology in which a higher voltage is converted to a lower voltage. Also known as a step-down switching regulator.

BUCK-BOOST REGULATOR

A switching regulator topology in which a positive voltage is converted to a negative voltage without a transformer.

DUTY CYCLE (D)

Ratio of the output switch's on-time to the oscillator period.

$$\begin{array}{ll} \textit{for buck regulator} & D = \frac{t_{ON}}{T} = \frac{V_{OUT}}{V_{IN}} \\ \\ \textit{for buck-boost regulator} & D = \frac{t_{ON}}{T} = \frac{|V_O|}{|V_O| + |V_{IN}|} \\ \end{array}$$

CATCH DIODE OR CURRENT STEERING DIODE

The diode which provides a return path for the load current when the LM2574 switch is OFF.

EFFICIENCY (n)

The proportion of input power actually delivered to the load.

$$\eta = \frac{P_{OUT}}{P_{IN}} = \frac{P_{OUT}}{P_{OUT} + P_{LOSS}}$$

CAPACITOR EQUIVALENT SERIES RESISTANCE (ESR)

The purely resistive component of a real capacitor's impedance (see *Figure 17*). It causes power loss resulting in capacitor heating, which directly affects the capacitor's operating lifetime. When used as a switching regulator output filter, higher ESR values result in higher output ripple voltages.




FIGURE 17. Simple Model of a Real Capacitor

Most standard aluminum electrolytic capacitors in the 100 μ F-1000 μ F range have 0.5 Ω to 0.1 Ω ESR. Higher-grade capacitors ("low-ESR", "high-frequency", or "low-inductance") in the 100 μ F-1000 μ F range generally have ESR of less than 0.15 Ω .

EQUIVALENT SERIES INDUCTANCE (ESL)

The pure inductance component of a capacitor (see *Figure 17*). The amount of inductance is determined to a large extent on the capacitor's construction. In a buck regulator, this unwanted inductance causes voltage spikes to appear on the output.

OUTPUT RIPPLE VOLTAGE

The AC component of the switching regulator's output voltage. It is usually dominated by the output capacitor's ESR multiplied by the inductor's ripple current ($\Delta I_{\rm IND}$). The peak-to-peak value of this sawtooth ripple current can be determined by reading the Inductor Ripple Current section of the Application hints.

CAPACITOR RIPPLE CURRENT

RMS value of the maximum allowable alternating current at which a capacitor can be operated continuously at a specified temperature.

STANDBY QUIESCENT CURRENT (I_{STBY})

Supply current required by the LM2574 when in the standby mode $(\overline{ON}/OFF$ pin is driven to TTL-high voltage, thus turning the output switch OFF).

INDUCTOR RIPPLE CURRENT (ΔI_{IND})

The peak-to-peak value of the inductor current waveform, typically a sawtooth waveform when the regulator is operating in the continuous mode (vs. discontinuous mode).

Definition of Terms (Continued)

CONTINUOUS/DISCONTINUOUS MODE OPERATION

Relates to the inductor current. In the continuous mode, the inductor current is always flowing and never drops to zero, vs. the discontinuous mode, where the inductor current drops to zero for a period of time in the normal switching cycle.


INDUCTOR SATURATION


The condition which exists when an inductor cannot hold any more magnetic flux. When an inductor saturates, the inductor appears less inductive and the resistive component dominates. Inductor current is then limited only by the DC resistance of the wire and the available source current.


OPERATING VOLT MICROSECOND CONSTANT (E•Top)

The product (in Volt•µs) of the voltage applied to the inductor and the time the voltage is applied. This E•T_{op} constant is a measure of the energy handling capability of an inductor and is dependent upon the type of core, the core area, the number of turns, and the duty cycle.

Physical Dimensions inches (millimeters) unless otherwise noted








M14B (REV D)

14-Lead Wide Surface Mount (WM) Order Number LM2574M-3.3, LM2574HVM-3.3, LM2574M-5.0, LM2574HVM-5.0, LM2574M-12, LM2574HVM-12, LM2574M-15, LM2574HVM-15, LM2574M-ADJ or LM2574HVM-ADJ NS Package Number M14B

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



Order Number LM2574M-3.3, LM2574HVM-3.3, LM2574HVN-5.0, LM2574HVN-12, LM2574HVN-15, LM2574HVN-ADJ, LM2574N-5.0, LM2574N-12, LM2574N-15 or LM2574N-ADJ **NS Package Number N08A**

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

For the most current product information visit us at www.national.com.

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT AND GENERAL COUNSEL OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

BANNED SUBSTANCE COMPLIANCE

National Semiconductor certifies that the products and packing materials meet the provisions of the Customer Products Stewardship Specification (CSP-9-111C2) and the Banned Substances and Materials of Interest Specification (CSP-9-111S2) and contain no "Banned Substances" as defined in CSP-9-111S2.



National Semiconductor Americas Customer Support Center

Email: new.feedback@nsc.com

Tel: 1-800-272-9959

www.national.com

National Semiconductor Europe Customer Support Center Fax: +49 (0) 180-530 85 86

Email: europe.support@nsc.com Deutsch Tel: +49 (0) 69 9508 6208 English Tel: +44 (0) 870 24 0 2171 Français Tel: +33 (0) 1 41 91 8790

National Semiconductor Asia Pacific Customer Support Center Email: ap.support@nsc.com **National Semiconductor** Japan Customer Support Center Fax: 81-3-5639-7507 Email: jpn.feedback@nsc.com Tel: 81-3-5639-7560

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products Applications

Audio www.ti.com/audio Communications and Telecom www.ti.com/communications **Amplifiers** amplifier.ti.com Computers and Peripherals www.ti.com/computers dataconverter.ti.com Consumer Electronics www.ti.com/consumer-apps **Data Converters DLP® Products** www.dlp.com **Energy and Lighting** www.ti.com/energy DSP dsp.ti.com Industrial www.ti.com/industrial Clocks and Timers www.ti.com/clocks Medical www.ti.com/medical Interface interface.ti.com Security www.ti.com/security

Logic Space, Avionics and Defense <u>www.ti.com/space-avionics-defense</u>

Power Mgmt power.ti.com Transportation and Automotive www.ti.com/automotive
Microcontrollers microcontroller.ti.com Video and Imaging www.ti.com/video

RFID <u>www.ti-rfid.com</u>
OMAP Mobile Processors www.ti.com/omap

Wireless Connectivity <u>www.ti.com/wirelessconnectivity</u>

TI E2E Community Home Page <u>e2e.ti.com</u>

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2011, Texas Instruments Incorporated