# SPECIFICATION FOR APPROVAL

承認

Description	:	Piezo Audio Indicator
Kingstate Part No.	:	KPEG251
Customer's Model No.	:	
Specification No.	:	PKD-7371
Number Of The Edition	:	1.1

CUSTOMER'S APPROVED SIGNATURE				

# 志豐電子股份有限公司 KINGSTATE ELECTRONICS CORP.



Address:10F, No. 69-11, Sec. 2, Chung Cheng E. Rd., Tamshui County, Taipei Hsien, Taiwan, R.O.C.

International sales dept.: TEL:886-2-2809-5651 FAX:886-2-2809-7151 Domestic sales dept: TEL:886-2-2809-0668 FAX:886-2-28096748

http://www.kingstate.com.tw

Approved by	Checked by	Issued by
TOTAL SOL	罗科的	Fei 7/04/05'


### A. SCOPE 範疇

This specification applies piezo audio indicator, **KPEG251** 此規格書適用於壓電式蜂鳴器, **KPEG251** 

## B. SPECIFICATION 規格

No.	Item	Unit	Specification	Condition
1	Operating Frequency 操作頻率	KHz	3.5 ± 0.5	
2	Operating Volt. range 操作電壓範圍	VDC	4~28	
3	Current consumption 消耗電流	mA	MAX 5	at 12VDC
4	Sound pressure level 輸出音壓	dB	MIN 82	at 30 cm/12VDC
5	Rated Voltage 額定電壓	VDC	12	
6	Tone 聲音		Fast Pulse (3.0Hz+20%) 快艷續音	at 12VDC
7	Operating temp. 操作温度		-30 ~ + 85	
8	Storage temp. 儲存溫度		-40 ~ + 95	
9	Dimension 尺寸	mm	28.0 x H25.4	See appearance drawing 請參照外觀尺寸圖
10	Weight (MAX) 重量	gram	10.1	
11	Material 材質		ABS UL-94 1/16" HB HIGH HEAT (BLACK)	
12	Terminal 端子		Wire type	See appearance drawing 請參照外觀尺寸圖
13	Environmental Protection Regulation 環保法規		RoHS	


# C. APPEARANCE DRAWING 外觀尺寸圖



Tol: ± 0.5 Unit: mm

### D. MEASURING METHOD 測量方法

S.P.L. Measuring Circuit 音壓測試接線圖




Mic: RION S.P.L meter UC30 or equivalent

Mic: RION 噪音計 UC30 或同等品

S.G: Hewlett Packard 33120A Function Generator or equivalent

S.G: Hewlett Packard 33120A 函數信號產生器或同等品

# E. VOLTAGE: SOUND PRESSURE LEVEL / VOLTAGE: CURRENT CONSUMPTION CHARACTERISTICS 電壓與音壓/電壓與耗電流之特性



志豐電子股份有限公司 KINGSTATE ELECTRONICS CORP 3/5 KPEG251

# F. MECHANICAL CHARACTERISTICS 機械特性

No.	Item	Test Condition	Evaluation standard	
1	Solderability 焊錫附著性 (Connector excepted) (端子類不適用此項)	Stripped wires of lead wires are immersed in rosin for 5 seconds and then immersed in solder bath of +270±5 for 3±0.5 seconds. 裸線部份浸入松香溶液 5 秒後,再浸入+270±5 溶射焊線槽 3±0.5 秒.	90% min. stripped wires shall be wet with solder.(Except the edge of terminal) 浸入裸線部份附著焊錫 90%以上(末端斷面不算)	
2	Lead Wire Pull Strength 線材拉力	The pull force shall be applied to double lead wire: Horizontal 3.0N(0.306kg) for 30 seconds. Vertical 2.0N(0.204kg) for 30 seconds. 雙線材水平方向施以3.0N(0.306kg)的力量, 垂直方向施以 2.0N(0.204kg)的力量,各30秒.	No damage and cutting off. 線材不鬆動,不脫落.	
3	Vibration 振動活式競	Buzzer shall be measured after being applied vibration of amplitude of 1.5mm with 10 to 55hz band of vibration frequency to each of 3 per-pendicular directions for 2 hours. 振動過波數 10 55HZ、全振幅 1.5mm 於 X.Y.Z 3 個方向,各 2 小時.	frequency/ current consumption should be in ±10% compared with initial ones .The SPL should	
4	Drop test 落下測試	The part only shall be dropped from a height of 75cm onto a 40mm thick wooden board 3 times in 3 axes (X.Y.Z). (a total of 9 times). 單體從75 公分高處, X.Y.Z.3 個方向,各3回,落於40mm厚木板上.	be in ±10dB compared with initial one. 諧振頻率與消耗電流變化量須在 ±10%內. 輸出音壓變化量須在 ±10dB內.	

# G. ENVIRONMENT TEST 環境測試

No.	Item	Test Condition	Evaluation standard
1	High temp. test 高溫測試	After being placed in a chamber at +95 for 240 hours 置於+95 環境中 240 小時	
2	Low temp. test 低溫測試	After being placed in a chamber at -40 for 240 hours 置於-40 環境中 240 小時	
3	Humidity test 相對濕度測試	After being placed in a chamber at +40 and 90±5% relative humidity for 240 hours 置於+40 ,相對濕度 90±5% 環境中 240 小時	Being placed for 4 hours at +25, buzzer shall be
4	Temp. cycle test 溫度循環試驗	The part shall be subjected to 5 cycles. One cycle shall be consist of: 單體承受溫度循環測試 5 次,其循環內容如圖示:  +95  -40  0.5hr 0.5hr 0.25 0.5hr 0.5hr 0.5hr 0.25  3hours	measured. The value of oscillation frequency/ current consumption should be in±10% compared with initial ones. The SPL should be in±10dB compared with initial one. 經測試後,靜置於+25 (室溫)環境中4小時後,諧振頻率與消耗電流變化量須在±10%內. 輸出音壓變化量須在±10dB內.

### H. RELIABILITY TEST 信賴性測試

No.	Item	Test condition	Evaluation standard
1	Operating life test 壽命測試	48 hours continuous operation at +/0 with rated voltage applied. 在+70 環境下,以額定電壓連續操作 48 小時.	Being placed for 4 hours at +25 , buzzer shall be measured. The value of oscillation frequency/ current consumption should be in ±10% compared with initial ones . The SPL should be in ±10dB compared with initial one. 經測試後,靜置於+25 (室溫)環境中4小時後,諧振頻率與消耗電流變化量須在±10%內. 輸出音壓變化量須在±10dB內.

#### **TEST CONDITION.**

Standard Test Condition 一般測試條件

a) 温度:+5~+35

b) 濕度:45-85% a) Temperature:  $+25 \pm 2$  b) Humidity: 60-70%


a) Temperature :  $+5 \sim +35$  b) Humidity : 45-85% c) Pressure : 860-1060mbar c) 氣壓: 860-1060mbar c) Pressure : 860-1060mbar c) 氣壓: 860-1060mbar


Judgement Test Condition 爭議時測試條件

a) 温度:+25±2

b) 濕度:60-70%

### I. PACKING STANDARD 包裝規格





310mmx248mmx49mm

550mmx330mmx290mm

1x90PCS=90PCS

90PCSx10=900PCS

Out Box

Carton Box