





Safety Data Sheet

LLG-Desiccant beads 1 to 3 mm
UWWcfX]b['hc FY[i `Ur]cb'f97Ł'Bc'% \$+#8\$\$*

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LLG-Desiccant beads 1 to 3 mm orange self-indicating gel (Part code: 9042587)

1.2. Details of the supplier of the safety data sheet

Company name: Lab Logistics Group GmbH

Street: Am Hambuch 1

Place: D-53340 Meckenheim

Telephone: 02225 9211-0

e-mail: info@llg-labware.com Internet: www.llg-labware.com

1.3. Emergency telephone number: 02225 / 9211-48

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

This substance is not classified as hazardous according to Regulation (EC) No. 1272/2008.

2.2. Label elements

SECTION 3: Composition/information on ingredients

3.1. Substances

Chemical characterization

SILICA

Sum formula: O2Si (Hill)
Molecular weight: 60,09

Hazardous components

CAS No	Chemical name				
	EC No	Index No	REACH No		
	Classification according to Regulation (EC) No. 1272/2008 [CLP]				
7631-86-9	amorphous silica			95- <100 %	
	amorphicus sinica			00 1100 70	
	231-545-4		01-2119379499-16-XXXX	00 1100 70	

Full text of H and EUH statements: see section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Postal address
Lab Logistics Group GmbH
Am Hambuch 1
D-53340 Meckenheim

Phone +49 (0)22 25/92 11-0 Fax +49 (0)22 25/92 11-11 Web www.LLG.de E-mail info@LLG.de General manager Michael Simon Tax identification number DE 812727887 Commercial register
No. HRB 10800
Court of registration
Bonn









After inhalation

Provide fresh air.

After contact with skin

Wash with water.

After contact with eyes

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist.

After ingestion

Rinse mouth immediately and drink plenty of water. Do NOT induce vomiting. In case of accident or unwellness, seek medical advice immediately (show directions for use or safety data sheet if possible).

4.2. Most important symptoms and effects, both acute and delayed

N.I.

4.3. Indication of any immediate medical attention and special treatment needed

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Co-ordinate fire-fighting measures to the fire surroundings. Suitable extinguishing media: Carbon dioxide (CO2). Water spray jet

Larger fires: alcohol resistant foam. Water spray jet

Unsuitable extinguishing media

not known

5.2. Special hazards arising from the substance or mixture

Ambient fire may liberate hazardous vapors.

5.3. Advice for firefighters

Use self-contained breathing apparatus.

Additional information

non flammable

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Do not breathe dust.

6.2. Environmental precautions

No special measures are necessary.

6.3. Methods and material for containment and cleaning up

Take up mechanically.

Avoid dust formation.

Treat the recovered material as prescribed in the section on waste disposal.

Provide adequate ventilation.

6.4. Reference to other sections

Safe handling: see section 7

Personal protection equipment: see section 8

Disposal: see section 13

SECTION 7: Handling and storage

Am Hambuch 1

7.1. Precautions for safe handling



General manager

Michael Simon

DF 812727887

Tax identification number









Advice on safe handling

Avoid dust formation.

Provide adequate ventilation.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

not known

Advice on storage compatibility

Store away from foodstuffs.

Further information on storage conditions

Keep container tightly closed and dry.

7.3. Specific end use(s)

NΙ

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Additional advice on limit values

The valid during the making lists serve as a basis.

8.2. Exposure controls

Protective and hygiene measures

Remove contaminated, saturated clothing immediately.

Do not breathe dust.

Wash hands before breaks and after work.

Eye/face protection

Tightly fitting goggles.

Hand protection

Wear protective gloves.

Thickness of the glove material NBR (Nitrile rubber): > 0,11 mm

The quality of the protective gloves resistant to chemicals must be chosen as a function of the specific working place concentration and quantity of hazardous substances.

Breakthrough time (maximum wearing time) Value for the permeation: Level = 6

Skin protection

Protective clothing

Respiratory protection

Respiratory protection necessary at: dust formation Filtering device with filter or ventilator filtering device of type: P2

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state: pearls

Colour: colourless - brown

Odour: odourless

Test method

pH-Value: 4 ~ 9

Changes in the physical state

Melting point: N.I. Initial boiling point and boiling range: $\sim 2980 \, ^{\circ}\text{C}$

Lab Logistics Group GmbH Am Hambuch 1 D-53340 Meckenheim Phone +49 (0)22 25/92 11-0 Fax +49 (0)22 25/92 11-11 Web www.LLG.de E-mail info@LLG.de General manager Commercial register
Michael Simon No. HRB 10800
Tax identification number
DE 812727887 Bonn









Flammability

Solid: Non-flammable. Gas: Non-flammable. Lower explosion limits: N.I.

Upper explosion limits: N.I. Ignition temperature: N.I.

Auto-ignition temperature Solid: N.I. Gas: N.I. Vapour pressure: N.I. N.I. Density: 400-900 kg/m³ Bulk density: Water solubility: insoluble Partition coefficient: N.I. Viscosity / dynamic: N.I. Viscosity / kinematic: N.I. N.I. Vapour density:

Evaporation rate: There are no details.

9.2. Other information

N.I.

SECTION 10: Stability and reactivity

10.2. Chemical stability

No decomposition if used according to specifications.

10.3. Possibility of hazardous reactions

Violent reaction with: Incompatible materials

10.4. Conditions to avoid

N.I.

10.5. Incompatible materials

sodium / Heat, difluoride, Hydrogen fluoride, xenon hexafluoride

10.6. Hazardous decomposition products

N.I.

Further information

hygroscopic

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

Physiologically inert substance that no hazardous properties shows. Physiologically inert substance that no hazardous properties shows.

When used and handled according to specifications Use caused the product to our experience and the information provided to us, no adverse health effects.

This substance is classified as not hazardous according to 67/548/EEC.

Handle in accordance with good industrial hygiene and safety practice.









CAS No	Chemical name							
	Exposure routes	Method	Dose	Species	Source			
7631-86-9	amorphous silica							
	oral	LD50	>10000 mg/kg	Rat				
	dermal	LD50	>5000 mg/kg	Rabbit				

Irritation and corrosivity

Corrosion / irritation to the skin: Has degreasing effect on the skin.

Sensitising effects

not known

Severe effects after repeated or prolonged exposure

Aspiration hazard

Eye irritation possible

Inhalation of dust may cause irritation of the respiratory system.

SECTION 12: Ecological information

12.1. Toxicity

CAS No	Chemical name							
	Aquatic toxicity	Method	Dose	[h] [d]	Species	Source		
7631-86-9	amorphous silica							
	Acute fish toxicity	LC50	>10 000 mg/l		Brachydanio rerio (zebra-fish)			
	Acute crustacea toxicity	EC50	>10 000 mg/l	1	Daphnia magna (Big water flea)			

12.2. Persistence and degradability

N.I.

12.3. Bioaccumulative potential

N.I.

12.4. Mobility in soil

N.I.

12.5. Results of PBT and vPvB assessment

not applicable

Further information

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Advice on disposal

Dispose of waste according to applicable legislation.

Contaminated packaging

Dispose of waste according to applicable legislation.

SECTION 14: Transport information

Am Hambuch 1

Land transport (ADR/RID)

14.1. UN number:











Product code: 100076

No dangerous good in sense of these transport regulations. 14.2. UN proper shipping name:

Inland waterways transport (ADN)

14.1. UN number:

14.2. UN proper shipping name: No dangerous good in sense of these transport regulations.

Marine transport (IMDG)

14.1. UN number:

14.2. UN proper shipping name: No dangerous good in sense of these transport regulations. -

Air transport (ICAO)

14.1. UN number:

14.2. UN proper shipping name: No dangerous good in sense of these transport regulations.

14.6. Special precautions for user

N.I.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulatory information

Water contaminating class (D): - - not water contaminating

15.2. Chemical safety assessment

For this substance a chemical safety assessment has not been carried out.

SECTION 16: Other information

Abbreviations and acronyms

n / A. = Not applicable N.B. = Not otherwise specified K.I. = No information available

Meckenheim, 2020-10-02

This document was sent online and is valid without signature

No. HRB 10800 Court of registration



