

## Solid carbide end mill

4 cutting edges, TiAlN-coated

**ORION**<sup>®</sup>

### Application:

End mill for universal machining of non-ferrous metals.

### Execution:

- solid carbide ultra-fine grain
- straight shank in accordance with DIN 6535 HB
- TiAlN-coated
- centre cutting
- with edge protection chamfer



<b>Art. no.</b>	<b>16828 120</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	16828120
<b>Cutting material</b>	SC
<b>Surface</b>	TiAlN
<b>Type</b>	W
<b>Number of cutting edges</b>	4 PCS
<b>Twist angle</b>	45°
<b>Tool holding device</b>	HB parallel shank
<b>Construction length</b>	Normal
<b>Cutting edge diameter</b>	12 mm
<b>Cutting edge length</b>	26 mm
<b>Length</b>	83 mm
<b>Edge protection chamfer length</b>	0.2 mm
<b>Shank diameter</b>	12 mm
<b>fz aluminium</b>	0.06 mm
<b>Gross Weight</b>	0.100 kg
<b>Overall stainless steel suitability</b>	2
<b>fitness not iron total</b>	1
<b>fitness Titan/Nickel/Super total</b>	2
<b>Product Group</b>	154

### EAN

4039247455584