

Crane pick-up magnet

Permanently high magnetic force

Application:

For the safe transport of sheet metal and steel parts by crane.

Execution:

- With a crane lug for crane operation
- For horizontal and vertical lifting
- Attached sheets of metal can be swivelled from a vertical position to a horizontal position and vice versa
- Board format 1000 x 2000 mm requires only 1 magnetic claw, board format 1500 x 3000 mm requires 2 pieces together with one spreader. When working with stacks of metal sheets, only 1 sheet may be lifted at a time.

Advantage:

- Entirely maintenance-free
- Permanently high magnetic force
- No magnetisation of workpieces



Art. no.	77350 050
Load-carrying capacity	300 kg
Suitable for min. sheet metal thickness	4 mm
Surface area length	290 mm
Surface area width	180 mm
Gross Weight	10.500 kg
Product Group	7EF