

# **Specification**

Part No.	:	CGGBP.35.2.A.08
Description	:	GPS/GLONASS/GALILEO/BeiDou
		L1 Embedded Patch Antenna 35x35x2mm
Features	:	Wide-band Operation L1 1559-1610MHz
		3.45dBi Peak Gain for BeiDou Band
		3.68dBi Peak Gain for GPS/GALILEO Band
		4.87dBi Peak Gain for GLONASS Band
		Low profile – 2mm Height
		Pin type Ceramic Patch Antenna
		Manufactured in an IATF16949 Approved Facility
		RoHS compliant





## **1. Introduction**

The CGGBP.35.2.A.08 is a ceramic GNSS L1 GPS/GLONASS/GALILEO/BeiDou embedded passive patch antenna, with a low profile of 2mm thickness. It is designed for professional applications in vehicle navigation devices as well as other M2M devices. Typical uses are in transportation, defense, marine, agriculture, and navigation.

Compared to using a smaller antenna, this will translate into the GNSS system having much higher location accuracy, improved reliability of lock in urban areas, better signal reception, with more satellites acquired and a quicker time to first fix. The CGGBP.35.2.A.08 is manufactured and tested in a TS16949 first tier automotive approved facility.

The patch is mounted via pin and double-sided adhesive. While the antenna will work very well in most device environments (Note cannot be covered with metal enclosure), tuning and further optimization of this antenna to different ground-planes and enclosures can be done if required, also including a pin length change, subject to possible NRE and minimum order quantity. Contact your local Taoglas sales office for more details.



## 2. Specification

Application Bands	BeiDou		GPS/GALILEO	GLONASS		
Frequency	1561.098±2.046MHz		1575.42 ±1.023MHz	1602±5MHz		
Efficiency	58.60 %		59.94 %	71.33%		
Peak Gain	3.45dBi		3.68dBi	4.87dBi		
Average Gain	Average Gain -2.32dBi		-2.22dBi	-1.47dBi		
Impedance			50 ohms			
MECHANICAL						
Ceramic Dimension			35.5 x 35.5 x 2mm			
Material			Ceramic			
Pin Diameter			0.85mm			
Pin Length			2.4mm			
Weight			8.6g			
ENVIRONMENTAL						
Operation Temperature			-40°C to 85°C			
Storage Temperature			-40°C to 105°C			
Humidity			Non-condensing 65°C 95% RH			

\* Antenna properties were measured with the antenna mounted on 70\*70mm Ground Plane



## **3. Antenna Characteristics**

#### 3.1. Return Loss



#### 3.2. **VSWR**





#### **3.3. Efficiency**



#### 3.4. Average Gain





#### 3.5. Peak Gain



#### 3.6. Smith Chart





## 4. Antenna Radiation Pattern

#### 4.1. Test Setup



SPE-16-8-075/B/AW Page 7 of 14



#### 4.2. 2D Radiation Pattern







SPE-16-8-075/B/AW Page 8 of 14





#### 4.3. 3D Radiation Pattern



1561MHz



1575.42MHz





1602MHz



## 5. Mechanical Drawing (Unit: mm)





#### **5.1. Adhesive Thickness**



Red Line shows the adhesive without Liner - thickness 0.08~0.1mm

#### **5.2. PCB Footprint Recommendation**





### 6. Packaging





Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.