



RJ45 ICM 1G Base-T Low Profile

Part No:

TMJK7036-1A98NL

Description:

RJ45 connector with integrated magnetics 1G Base-T Single Port Tab-UP with right angle THT mount and LED

Features:

AutoMDIX

3Wire CMC/Chip

Low Profile

EMI Finger

RoHS & REACH Compliant



	3
S	4
	5
	6
Storage	7
	8

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.













1. Introduction



Featuring a popular footprint and compatible package to industry RJ45 Integrated Connectors standards, the Taoglas TMJK7036-1A98NL is an RJ45 Integrated Connector 1G Base-T Single Port Tab Up with EMI Finger and 3Wire Common Mode Choke on the chip side that enables AutoMDIX feature.

Typical Applications Include:

- Industrial Automation
- Hubs
- Routers
- Switches
- Wireless Access Points

Taoglas Magnetics offer an extensive product line of RJ45 Integrated Connectors designed for commercial and industrial grade applications, supporting 10/100 Base-T (Atmos100 Series) and 1G Base-T (Atmos1000 series). These surface mount or through-hole components provide reliable performance and maintain signal integrity that meets IEEE 802.3 standards, and they are UL certified. The Power over Ethernet options are also available including PoE, PoE+ and PoE++.

The majority of Taoglas RJ45 ICMs are manufactured with fully automated winding, assembly & testing to ensure consistent performance, quality and reliability while ensuring cost competitiveness for its customers. These products are fully compliant with the REACH and RoHS directive, and compatible with all major PHY vendors.

For customized products or support with integration, contact your regional Taoglas customer support team for further information.



2. Specifications

Electrical Performance @25°C			
Inductance OCL	350μH MIN@100KHz 0.1V 8mA DC Bias		
Turns Ratio (±3%)	TX=1CT: 1CT	RX=1CT: 1CT	
Insertion Loss	-1.0dB MAX @ 1-100Mhz		
Return Loss	-18dB MIN	@ 1-30Mhz	
	-15dB MIN (@ 30-60Mhz	
	-12dB MIN @	9 60-100Mhz	
Cross talk	-40dB MIN	@ 1-30Mhz	
	-35dB MIN	@ 20-60Mhz	
	-30dB MIN @	9 60-100Mhz	
Common Mode Rejection	-30dB MIN	@ 1-50Mhz	
	-20dB MIN @	9 50-150Mhz	
Hi-Pot	1500	Vrms	

Environmental Specifications			
Operating Temperature	0°C TO +70°C		

Material Specifications			
Housing	Thermoplastic UL94V-0		
Contact	Copper alloy		
	Gold		
Contact Plating	Thickness = 6μ " min in contact area		
Shield	Nickel		


Compliance		
UL recognized - FILE NO. E528697		
RoHS Compliant		
IEEE 802.3		

Storage requirements			
Humidity	Storage Temperature		
MSL - 1	-40°C TO +85°C		




3. Mechanical

3.1 Mechanical Drawings








Mechanical Specifications			
Height Above Board	0.445" (11.3mm)		
Width	0.7" (17.78mm)		
Depth	0.946" (24.04mm)		
Mounting Style	Through Hole (THT)		
Mounting Angle	Right Angle		

Dimensions are in millimeters with the following tolerances: $X.XX = \pm 0.25$

3.2 PCB Layout




 $\label{eq:Suggested} Suggested\ PCB\ Layout\ (Top\ View)$ Dimensions are in millimeters with the following tolerances: X.XX = ± 0.10





4. Electrical

4.1 Electrical Drawings




LED Electrical Specification				
Standard LED	Wavelength (nm)	V_F (I_F =20mA)	$I_R (V_R=5v)$	
Green	565	1.8~2.6v	10 μA Max	
Yellow	585	1.8~2.6v	10 μA Max	
Orange	610	1.8~2.6v	10 μA Max	





4.2 Profile of Wave Solder






5. Packaging and Storage

5.1 SPQ

50 pcs/tray

Tray dimension: 299*163*23 mm


Tray Weight: 393g



1 CTN = 20 trays = 1000 pcs


Carton dimensions: 320*300*300mm

Carton Weight: 8.4kg





Changelog







www.taoglas.com

