

## knurl cutter HSSE-PM 30°

For use on knurl cutter tools 19100



### Application:


For producing straight knurls in accordance with DIN 82 RAA (in holders with 1 knurl) in steel, stainless steel, non-ferrous metals and cast iron material groups.

### Version:

- HSSE PM 30°, ground tooth flanks, uncoated

### Advantage:

- High precision with ground teeth and good cutting performance, even with difficult materials
- Very good surface quality and long service life with high-quality HSSE-PM cutting material



<b>Art. no.</b>	<b>19171 206</b>
<b>Knurling wheel diameter</b>	14.5 mm
<b>Partition</b>	0.6 mm
<b>Machining direction</b>	Left
<b>Surface</b>	Uncoated