


## GE-R Male stud connector

Male BSPP thread – metal sealing edge (ISO 1179) / EO 24° cone end



Series	D1	T	D3	D4	L1	L2	L3	L4	S1	S2	Weight g/1 piece	Order code*	PN (bar) <sup>1)</sup>		
													CF	71	MS
L <sup>3)</sup>	06	G 1/8 A	4	14	23.5	8.5	8	23.0	14	14	14	GE06LR	315	315	200
	06	G 1/4 A	4	18	29.0	10.0	12	25.0	19	14	60	GE06LR1/4	315	315	200
	06	G 3/8 A	4	22	30.5	11.5	12	26.0	22	14	45	GE06LR3/8	315	315	200
	06	G 1/2 A	4	26	33.0	12.0	14	27.0	27	14	60	GE06LR1/2	315	315	
	08	G 1/4 A	6	18	29.0	10.0	12	25.0	19	17	26	GE08LR	315	315	200
	08	G 1/8 A	4	14	24.5	8.5	8	23.0	14	17	16	GE08LR1/8	315	315	
	08	G 3/8 A	6	22	30.5	11.5	12	26.0	22	17	44	GE08LR3/8	315	315	200
	08	G 1/2 A	6	26	33.0	12.0	14	27.0	27	17	74	GE08LR1/2	315	315	200
	10	G 1/4 A	6	18	30.0	11.0	12	26.0	19	19	31	GE10LR	315	315	200
	10	G 1/8 A	4	14	25.5	10.5	8	25.0	17	19	21	GE10LR1/8	315	315	
10	G 3/8 A	8	22	31.5	12.5	12	27.0	22	19	44	GE10LR3/8	315	315	200	
10	G 1/2 A	8	26	34.0	13.0	14	28.0	27	19	72	GE10LR1/2	315	315	200	
12	G 3/8 A	9	22	31.5	12.5	12	27.0	22	22	43	GE12LR	315	315	200	
12	G 1/8 A	4	14	26.5	11.5	8	26.0	19	22	27	GE12LR1/8	315	315		
12	G 1/4 A	6	18	31.0	12.0	12	27.0	19	22	32	GE12LR1/4	315	315	200	
12	G 1/2 A	10	26	34.0	13.0	14	28.0	27	22	67	GE12LR1/2	315	315	200	
12	G 3/4 A	10	32	37.0	14.0	16	29.0	32	22	120	GE12LR3/4	315	315		
15	G 1/2 A	11	26	35.0	14.0	14	29.0	27	27	72	GE15LR	250	250	160	
15	G 3/8 A	9	22	32.5	13.5	12	29.0	24	27	56	GE15LR3/8	250	250	160	
15	G 3/4 A	12	32	38.0	15.0	16	30.0	32	27	118	GE15LR3/4	250	250		
18	G 1/2 A	14	26	36.0	14.5	14	31.0	27	32	72	GE18LR	250	250	160	
18	G 3/8 A	9	22	33.5	14.0	12	29.5	27	32	69	GE18LR3/8	250	250		
18	G 3/4 A	15	32	38.0	14.5	16	30.0	32	32	112	GE18LR3/4	250	250		
22	G 3/4 A	18	32	40.0	16.5	16	33.0	32	36	103	GE22LR	160	160	100	
22	G 1/2 A	14	26	38.0	16.5	14	33.0	32	36	91	GE22LR1/2	160	160	100	
22	G 1 A	19	39	43.0	17.5	18	33.5	41	36	184	GE22LR1	160	160		
28	G 1 A	23	39	43.0	17.5	18	34.0	41	41	168	GE28LR	160	160	100	
28	G 1/2 A	14	26	39.0	17.5	14	34.0	41	41	141	GE28LR1/2	160	160		
28	G 3/4 A	18	32	41.0	17.5	16	34.0	41	41	156	GE28LR3/4	160	160		
28	G 1 1/4 A	24	50	46.0	18.3	20	35.0	50	41	314	GE28LR11/4	160	160		
35	G 1 1/4 A	30	49	48.0	17.5	20	39.0	50	50	276	GE35LR	160	160	100	
35	G 1/2 A	14	26	42.0	17.5	14	39.0	46	50	194	GE35LR1/2	160	160		
35	G 3/4 A	18	32	44.0	17.5	16	39.0	46	50	202	GE35LR3/4	160	160		
35	G 1 A	23	39	46.0	17.5	18	39.0	46	50	234	GE35LR1	160	160		
35	G 1 1/2 A	30	55	52.0	19.5	22	41.0	55	50	355	GE35LR11/2	160	160		
42	G 1 1/2 A	36	55	52.0	19.0	22	42.0	55	60	349	GE42LR	160	160	100	
42	G 1 A	23	39	48.0	19.0	18	42.0	55	60	327	GE42LR1	160	160		
42	G 1 1/4 A	30	49	50.0	19.0	20	42.0	55	60	336	GE42LR11/4	160	160		

<sup>1)</sup> Pressure shown = item deliverable

<sup>3)</sup> L = light series

$$\frac{\text{PN (bar)}}{10} = \text{PN (MPa)}$$


Delivery without nut and ring. Information on ordering complete fittings see page I7.

\*Please add the **suffixes** below according to the material/surface required.

Order code suffixes		
Material	Suffix surface and material	Example
Steel, zinc plated, Cr(VI)-free	CFX	GE18LR CFX
Stainless Steel	71X	GE18LR 71X
Brass	MSX	GE18LR MSX

## GE-R Male stud connector

Male BSPP thread – metal sealing edge (ISO 1179) / EO 24° cone end



Series	D1	T	D3	D4	L1	L2	L3	L4	S1	S2	Weight g/1 piece	Order code*	PN (bar) <sup>1)</sup>		
													CF	71	MS
S <sup>4)</sup>	06	G 1/4 A	4	18	32.0	13.0	12	28	19	17	35	<b>GE06SR</b>	400	400	250
	06	G 1/8 A	3	14	27.5	12.5	8	27	14	17	22	<b>GE06SR1/8</b>	400	400	
	06	G 3/8 A	4	22	34.5	15.5	12	30	22	17	57	<b>GE06SR3/8</b>	400	400	
	06	G 1/2 A	4	26	39.0	18.0	14	33	27	17	83	<b>GE06SR1/2</b>	400	400	
	08	G 1/4 A	5	18	34.0	15.0	12	30	19	19	41	<b>GE08SR</b>	400	400	250
	08	G 3/8 A	5	22	34.5	15.5	12	30	22	19	59	<b>GE08SR3/8</b>	400	400	
	08	G 1/2 A	5	26	39.0	18.0	14	33	27	19	100	<b>GE08SR1/2</b>	400	400	
	10	G 3/8 A	7	22	34.5	15.0	12	31	22	22	56	<b>GE10SR</b>	400	400	250
	10	G 1/4 A	5	18	34.0	14.5	12	31	19	22	43	<b>GE10SR1/4</b>	400	400	
	10	G 1/2 A	7	26	39.0	17.5	14	34	27	22	97	<b>GE10SR1/2</b>	400	400	
	12	G 3/8 A	8	22	36.5	17.0	12	33	22	24	62	<b>GE12SR</b>	400	400	250
	12	G 1/4 A	5	18	36.0	16.5	12	33	22	24	57	<b>GE12SR1/4</b>	400	400	
	12	G 1/2 A	8	26	39.0	17.5	14	34	27	24	57	<b>GE12SR1/2</b>	400	400	
	14	G 1/2 A	10	26	41.0	19.0	14	37	27	27	96	<b>GE14SR</b>	400	400	250
	14	G 3/8 A	8	22	38.5	18.5	12	36	24	27	74	<b>GE14SR3/8</b>	400	400	
	16	G 1/2 A	12	26	41.0	18.5	14	37	27	30	92	<b>GE16SR</b>	400	400	250
16	G 3/8 A	8	22	38.5	18.0	12	36	27	30	83	<b>GE16SR3/8</b>	400	400		
16	G 3/4 A	12	32	45.0	20.5	16	39	32	30	157	<b>GE16SR3/4</b>	400	400		
20	G 3/4 A	16	32	47.0	20.5	16	42	32	36	151	<b>GE20SR</b>	400	400	250	
20	G 1/2 A	12	26	45.0	20.5	14	42	32	36	142	<b>GE20SR1/2</b>	400	400		
20	G 1 A	16	39	51.0	22.5	18	44	41	36	273	<b>GE20SR1</b>	250	250	160	
20	G 1 1/4 A	16	49	53.0	22.5	20	44	50	36	387	<b>GE20SR11/4</b>	160	160		
25	G 1 A	20	39	53.0	23.0	18	47	41	46	267	<b>GE25SR</b>	250	250		
25	G 3/4 A	16	32	51.0	23.0	16	47	41	46	245	<b>GE25SR3/4</b>	250	250		
25	G 1 1/4 A	20	49	55.0	23.0	20	47	50	46	422	<b>GE25SR11/4</b>	160	160		
30	G 1 1/4 A	25	49	57.0	23.5	20	50	50	50	422	<b>GE30SR</b>	160	160	100	
30	G 1 A	20	39	55.0	23.5	18	50	46	50	337	<b>GE30SR1</b>	160	160		
38	G 1 1/2 A	32	55	64.0	26.0	22	57	55	60	560	<b>GE38SR</b>	160	160	100	
38	G 1 1/4 A	25	49	62.0	26.0	20	57	55	60	578	<b>GE38SR11/4</b>	160	160		

1) Pressure shown = item deliverable

4) S = heavy series

$$\frac{\text{PN (bar)}}{10} = \text{PN (MPa)}$$

Delivery without nut and ring. Information on ordering complete fittings see page I7.

\*Please add the **suffixes** below according to the material/surface required.

Order code suffixes		
Material	Suffix surface and material	Example
Steel, zinc plated, Cr(VI)-free	CFX	GE16SRCFX
Stainless Steel	71X	GE16SR71X
Brass	MSX	GE16SRMSX