

Centre punches with cemented carbide tip

can be ground



Version:

- Ground and polished surface
- Painted shaft
- Octagonal profile with tempered safety hammer head
- Special tool steel, hardened
- Inlaid carbide tip can be ground



Art. no.	51298 010
Length	120 mm
Shank width x shank thickness	10 x 10 mm
Material	Chrome-vanadium steel

EAN-Code

4049002024245