

Belt sanding machine with abrasive disc Rasant



Application:

The belt sanding machine for horizontal and vertical grinding, with additional abrasive disc for sanding discs 350 mm in diameter (optionally with hook-and-loop fastening). Equipped with S1 motors for 100% switch-on time. The performance of S1 motors is around 40% greater than e.g. S6 motors.

Version:

- removable protective cover for surface grinding
- S1 three-phase motor 400 V, 50 Hz
- for surface and contact grinding
- low-vibration
- Connection for double suction system
- with emergency stop switch
- 24-volt safety device
- infinitely variable swivel-mounted workbench

Delivery:

With sanding belt, sanding disc 350 mm in diameter (self-adhesive) and connecting cable for optional fixed connection or CEE plug.



Art. no.	78236 320
Model	343/2
Max. sanding belt width	150 mm
Grinding belt length	1750 mm
Grinding disc dimension	350 mm
Total motor speed	1400/2800 rpm
Total engine capacity	1.27 / 1.7 kW
Total belt speed	15 / 30 m/s
Weight	145 kg

EAN-Code

4251770600280