

# SPALT-BLECHLOCHER TRICUT®

| Ø<br>in mm | Max.<br>Material-<br>stärke<br>in mm<br>(S235) | Größe<br>Metrisch | Größe<br>PG | Größe<br>Inch |       | Größe<br>Conduit<br>&<br>Pipe Size |  |  |  |  |
|------------|--|-------------------|-------------|---------------|-------|------------------------------------|---|---|---|---|
|            |  |                   |             | Art.-Nr.      |       |                                    |   |   |   |   |
| 12,5       | 1,5  | M 12              | 7           | 1/2"          | 0.500 | -                                  | 01674   | 01770   | 02022   | 01334   |
| 15,2       | 2,0  | -                 | 9           | -             | 0.598 | -                                  | 01680   | 01771   | 02003   | 01339   |
| 16,2       | 2,0  | M 16              | -           | -             | 0.638 | -                                  | 01683   | 01772   |   |   |
| 18,6       | 2,0  | -                 | 11          | -             | 0.732 | -                                  | 01686   | 01773   |   |   |
| 20,4       | 2,0  | M 20              | 13          | -             | 0.803 | -                                  | 01689   | 01774   |   |   |
| 22,5       | 2,0  | -                 | 16          | 7/8"          | 0.886 | 1/2"                               | 01692   | 01775   |   |   |
| 25,4       | 2,0  | M 25              | -           | 1"            | 1.000 | -                                  | 01695   | 01776   |   |   |
| 28,3       | 2,0  | -                 | 21          | -             | 1.114 | 3/4"                               | 01698   | 01777   |   |   |
| 28,3       | 3,0  | -                 | 21          | -             | 1.114 | 3/4"                               | 01701   | 01778   | 02002   | 01340   |
| 30,5       | 2,0  | -                 | -           | 1-7/32"       | 1.201 | -                                  | 01703   | 01779   | 02003   | 01339   |
| 32,5       | 3,0  | M 32              | -           | -             | 1.280 | -                                  | 01708   | 01780   | 02002   | 01340   |
| 34,6       | 3,0  | -                 | -           | 1-11/32"      | 1.362 | 1"                                 | 01711   | 01788   |   |   |
| 37,0       | 3,0  | -                 | 29          | -             | 1.457 | -                                  | 01713   | 01781   |   |   |
| 40,5       | 3,0  | M 40              | -           | -             | 1.594 | -                                  | 01715   | 01782   |   |   |
| 43,2       | 3,0  | -                 | -           | 1-11/16"      | 1.701 | 1 1/4"                             | 01718   | 01789   |   |   |
| 47,0       | 3,0  | -                 | 36          | -             | 1.850 | -                                  | 01720   | 01783   |   |   |
| 49,6       | 3,0  | -                 | -           | 1-15/16"      | 1.953 | 1 1/2"                             | 01723   | 01790   |   |   |
| 50,5       | 3,0  | M 50              | -           | -             | 1.988 | -                                  | 01736   | 01784   |   |   |
| 54,0       | 3,0  | -                 | 42          | 2-1/8"        | 2.126 | -                                  | 01727   | 01785   |   |   |
| 60,0       | 3,0  | -                 | 48          | -             | 2.362 | -                                  | 01729   | 01786   |   |   |
| 61,5       | 3,0  | -                 | -           | 2-3/8"        | 2.421 | 2"                                 | 01732   | 01791   | 01341   |   |
| 63,5       | 3,0  | M 63              | -           | 2-1/2"        | 2.500 | -                                  | 01739   | 01787   |   |   |