_	10	9		8	7		6	5	4
									A REF. THI
F									
	MALE FACE VIEW								
								(A)	
				5 —	4			.08	
						3		2.0	
	1			+	5				
E								2	
				45°				3	
						0			
						2			
				75	HEX -				
		—► .75 HI [19.0]							<b>-</b> .72 ──
									[18.3]
D									
								M12 X 1.0 -	
		/	<b>(8</b> )				<b>6</b>	THREAD	
				$\frown$		F)	•		ET .
_			<b>`</b>			$\overline{\mathbf{A}}$	Γ	_ሱ.ሎ.ሎ.	
			$\backslash$						
					—	-н Я			
				$\rightarrow$		Ā			
C									
		→ .75 HEX	-	→  .16				-	1.88
		19.0		3.9					47.8
								/	$\sim$
		DOTTING			7				
	9 8	POTTING HEXNUT	EPOXY BRASS	NICKEL PLATED			RIAL: AS NOTED H: AS NOTED		$\rangle$
В	8 7	LOCK-WASHER	STEEL	ZINC PLATED	<u>/</u>	NOTES:			
	6	GASKET	RUBBER	BLACK	-				FUNCTIONAL THIS DRAWING CONTAINS INFORMATION THA SYMBOLS DIMENSION UNITS SCALE CLIBRENT
	5	O-RING	NITRILE	RED	-	3. ELECTRIC			The second secon
	4	FEMALE INSERT	NYLON	BLACK	-	VOLTAGE; 60V AC/DC			GENERAL TOLERANCES (UNLESS SPECIFIED)
	3	PIN/SOCKET CONTACT		GOLD PLATED	1	CURRENT: 4A			
	2	MALE INSERT	NYLON	BLACK	1	5. PROTECT	ION: IP67 (WHEN MAT	TED)	DIVISIONAL SYMBOLS 2 PLACES + + CHK'D.
<u> </u>	1	RECEPTACLE SHELL	BRASS	NICKEL PLATED		6. ALL DIMS ARE FOR REFERENCE UNLESS			1 PLACE ± ± INITIAL
A	ITEM	DESCRIPTION	MATERIAL	FINISH		IULERAN			0 PLACES ± ± DRWN: ANGULAR TOL ± ° APPR:
F	RELEASE S	STATUS P1 RELEASE DATE 2	021/12/07 00:13	:14	-				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS
	T: IN-master-typrov ON: D1 2021/05/01	9		8	7		6	5	4

