



## Checktemp® 1

### Pocket thermometer with probe and one meter cable

This model offers the same outstanding features as its predecessor together with a stainless steel sharp probe ending in a one meter (3') cable. This makes Checktemp® 1 ideal for measuring liquids, air, frozen, solid and semi-solid materials, as well as those hard-to-reach places. To make the meter truly user-friendly, the display has been maximized to cover the entire width of the casing. The NTC sensor provides rapid response and excellent accuracy. One common AAA-type battery guarantees 3000 hours of continuous operation. That is over two years when using the meter for up to 4 hours a day! Fahrenheit models also available.

### Ordering Information

**HI 98509** (Checktemp® 1 C)  
supplied with 1.5V AAA battery and instructions.

**HI 98511** (Checktemp® 1 F)  
with 1.5V AAA battery, calibration certificate and instructions.

## Checktemp®-Dip

### Precision thermometer made with a stainless steel weighted probe

Checktemp®-Dip is an accurate instrument measuring temperature from -20 to 100°C (-4 to 212°F). The stainless steel probe with a three meter (9.9') cable is weighted so that it can be dipped into any vat and tank and measure the temperature at different depths. Due to its hygienic stainless steel probe, it is ideal for food applications, especially to check the temperature inside wine casks and milk tanks.

Because of its rugged construction and the long cable, you no longer have to bend down or get into awkward positions to measure the temperature. Simply drop the probe from a comfortable position and read the temperature on the large LCD display.

Checktemp®-Dip can also be used for applications such as fish farms, water reservoirs and pools where the operator can simply stand on the edge of the water and throw the probe over. The accuracy, in spite of the longer probe lead, is an excellent  $\pm 0.5^{\circ}\text{C}$  from -20 to 50°C (-4 to 122°F). In addition, you can check to make sure that your thermometer is measuring the right temperature with **Hanna's exclusive Cal-check** technology. As with the conventional Checktemp® meters, the battery life is a remarkable 3000 hours with a normal AAA type battery.

### Ordering Information

**HI 98509-01** (Checktemp®-Dip C)  
supplied with weighted probe, 3 m (9.9') cable, 1.5V AAA battery and instructions.

**HI 98510-01** (Checktemp®-Dip F)  
supplied with weighted probe, 3 m (9.9') cable, 1.5V AAA battery and instructions.



Checktemp®-Dip with its heavy probe and 3 meter cable makes measurements in vats and tanks simple

### Specifications

Checktemp®-Dip	
RANGE	-20.0 to 100.0°C
RESOLUTION	0.1°C
ACCURACY	$\pm 0.5^{\circ}\text{C}$ (-20 to 50°C)
PROBE	Stainless steel, 3 m (10') cable
BATTERY TYPE/LIFE	1 x 1.5V AAA / approx. 3000 hrs continuous use
ENVIRONMENT	0 to 50°C (32 to 122°F); RH 95%
DIMENSIONS	106 x 58 x 19 mm (4.2 x 2.2 x 0.7")
WEIGHT	80 g (2.8 oz.) (meter only)



For detailed information about this product see page B 25.