

Collet chucks type ER40 in accordance with DIN 6499 A

UP = ultra precision, concentricity < 2 µm

ATORN[®]

Application

For use on precision collet chucks

Advantage

- Higher concentricity extends tool life

Art. No.	23388 249
Collet type	ER 40
Clamping diameter	7.5 mm
Min./max. clamping range	3-26 mm
Outer diameter	41 mm
Length	46 mm
Clamping bypass	-0.5 mm



EAN-Code

4050293632019