

Precision pointer micrometer

MAHR 40 F

Mahr

Application:

For quick testing of parts from series production.

Version:

- Adjustable tolerance marks
- carbide-tipped measuring faces
- Movable measuring probe for lifting the anvil

Delivery:

in case



Art. no.	31472 005
Min./max. length measuring range	0-25 mm
Indicating calliper measuring range	+/- 0,065 mm
Digit increment, micrometer	0.01 mm
Digit increment, indicating calliper	0.001 mm
Micrometer error limit	0.002 mm
Indicating calliper error limit	0.001 mm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Measurement force	9 N
Measuring surface diameter	7.5 mm
Calibration Group	AN
DIN	863

EAN-Code

4059192004248