

Transverse drive shell end mill arbor DIN 6357 (face mill arbor)

With enlarged collar diameter, ISO-7388-1

ATORN[®]

Version

- Alloyed case-hardening steel, tensile strength in the core min. 950 N/mm²
- Internal coolant supply
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm
- max. concentricity < 0.005 mm
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080

Delivery

includes key blocks and cutter retaining screw



Art. no.	23162 183
Tool holding device	SK 40
Form	AD
Mandrel diameter	32 mm
Tap length	24 mm
Projecting length	100 mm
Outer diameter	78 mm
Balancing quality	G 2.5 at 25 rpm
Coolant supply	Internal axial

EAN-Code

4050293712179